

[See all 49 Products in Family](#)

**TECHSPEC® 3X, 40mm WD CompactTL™ Telecentric Lens**



40mm WD, 3X, In-Line Version (Left) and MS Version (Right)



Stock #63-747 **2 In Stock**

⊖ 1 ⊕ MRP ₹30,722

● Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹30,722 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

CompactTL™ Series **Product Family:**

Edmund Optics® **Manufacturer:**

Telecentric Lens **Type:**

## Physical & Mechanical Properties

|       |                                |
|-------|--------------------------------|
| Fixed | Iris Option:                   |
| 48.00 | Length (mm):                   |
| 48.00 | Length excluding Threads (mm): |
| 18.00 | Maximum Diameter (mm):         |
| 32    | Weight (g):                    |

## Optical Properties

|                          |  |
|--------------------------|--|
| 2.9mm                    | Horizontal Field of View, 2/3" Sensor: |
| 2.1mm                    | Horizontal Field of View, 1/2" Sensor: |
| 1.6mm                    | Horizontal Field of View, 1/3" Sensor: |
| 11.00                    | Maximum Image Circle (mm):             |
| 0.093                    | Numerical Aperture NA, Object Side:    |
| ±1                       | Working Distance Tolerance (mm):       |
| 5 (3)                    | Number of Elements (Groups):           |
| 0.076                    | Typical Telecentricity @ 588nm (°):    |
| 0.1697                   | Typical Distortion @ 588nm (%):        |
| 3X                       | Primary Magnification PMAG:            |
| 3.00                     | Telecentric Lens Magnification:        |
| 40                       | Working Distance (mm):                 |
| 2.9 x 2.2                | FOV @ Max Sensor Format, H x V (mm):   |
| f/16                     | Aperture (f/#):                        |
| M4 MgF <sub>2</sub>      | Coating:                               |
| ±0.08mm (20% @ 20 lp/mm) | Depth of Field (mm):                   |
| 3X                       | Magnification:                         |
| VIS                      | Lens Wavelength Range:                 |

## Sensor

|      |                        |
|------|------------------------|
| 2/3" | Maximum Sensor Format: |
| 4.50 | Pixel Size (µm):       |

## Threading & Mounting

|                                    |                        |
|------------------------------------|------------------------|
| M25.5 x 0.50 (Female)              | Filter Thread:         |
| <a href="#">#88-212 (Required)</a> | Filter Thread Adapter: |
| C-Mount                            | Mount:                 |

## Regulatory Compliance

|                           |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | REACH 241:                  |
|                           | Country of Origin:          |

**Imported By:**

Edmund Optics India Private Limited  
 267, Greystone Building, Second Floor,  
 6th Cross Rd, Binnamangala,  
 Stage 1, Indiranagar, Bengaluru,  
 Kamataka, India 560038  
 Phone: +91- 80-6845 0000

**Product Details**


- 2/3", C-Mount Telecentric Lens
- Up to 2.3 MegaPixels, 4.5µm Pixel Size Sensors
- Small Telecentric Lens with Coaxial Illumination Options

TECHSPEC® CompactTL™ Telecentric Lenses are designed for applications with tight space constraints due to their ultra-compact design. These lenses feature a 2/3" sensor format and a variety of different working distance and magnification options. From single unit to high volume implementation, these lenses provide a great price to performance ratio. TECHSPEC® CompactTL™ Telecentric Lenses are perfect for integration into gauging systems due to their excellent telecentricity and low distortion. The fixed iris and lockable focus make these lenses ideal for implementation into factory floors and assembly lines, as they will remain fixed over time.


**Technical Information**




#63-747, 3X, 40mm WD CompactTL™ Telecentric Lens , Distortion Plot




#63-747, 3X, 40mm WD CompactTL™ Telecentric Lens , Relative Illumination Plot



#63-747, 3X, 40mm WD CompactTL™ Telecentric Lens , Telecentricity Plot



#63-747, 3X, 40mm WD CompactTL™ Telecentric Lens , Modulated Transfer Function (MTF) Plot, 40mm Working Distance, f16



#63-747, 3X, 40mm WD CompactTL™ Telecentric Lens , Depth of Field Plot, 40mm Working Distance, f16