

[See all 49 Products in Family](#)

TECHSPEC® 3X, 65mm WD CompactTL™ Telecentric Lens



65mm WD, 3X, In-Line Version (Left) and MS Version (Right)



Stock **#63-735** **2 In Stock**

1 MRP ₹30,722

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹30,722 each
Need More?	Request Quote

Product Downloads

General

CompactTL™ Series **Product Family:**

Edmund Optics® **Manufacturer:**

Telecentric Lens **Type:**

Physical & Mechanical Properties

Fixed	Iris Option:
76.30	Length (mm):
76.30	Length excluding Threads (mm):
18.00	Maximum Diameter (mm):
44	Weight (g):

Optical Properties

2.9mm	Horizontal Field of View, 2/3" Sensor:
2.1mm	Horizontal Field of View, 1/2" Sensor:
1.6mm	Horizontal Field of View, 1/3" Sensor:
11.00	Maximum Image Circle (mm):
0.068	Numerical Aperture NA, Object Side:
±1	Working Distance Tolerance (mm):
5 (3)	Number of Elements (Groups):
0.015	Typical Telecentricity @ 588nm (°):
0.2689	Typical Distortion @ 588nm (%):
3X	Primary Magnification PMAG:
3.00	Telecentric Lens Magnification:
65	Working Distance (mm):
2.9 x 2.2	FOV @ Max Sensor Format, H x V (mm):
f/21.9	Aperture (f#):
M4 MgF ₂	Coating:
±0.12mm (20% @ 20 lp/mm)	Depth of Field (mm):
3X	Magnification:
VIS	Lens Wavelength Range:

Sensor

2/3"	Maximum Sensor Format:
4.50	Pixel Size (µm):

Threading & Mounting

M25.5 x 0.50 (Female)	Filter Thread:
#88-212 (Required)	Filter Thread Adapter:
M16 x 0.5 (Female)	Front Thread:
C-Mount	Mount:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Country of Origin:

China

Imported By:


Edmund Optics India Private Limited
 267, Greystone Building, Second Floor,
 6th Cross Rd, Binnamangala,
 Stage 1, Indiranagar, Bengaluru,
 Karnataka, India 560038
 Phone: +91-80-6845 0000

Product Details


- 2/3", C-Mount Telecentric Lens
- Up to 2.3 MegaPixels, 4.5µm Pixel Size Sensors
- Small Telecentric Lens with Coaxial Illumination Options

TECHSPEC® CompactTL™ Telecentric Lenses are designed for applications with tight space constraints due to their ultra-compact design. These lenses feature a 2/3" sensor format and a variety of different working distance and magnification options. From single unit to high volume implementation, these lenses provide a great price to performance ratio. TECHSPEC® CompactTL™ Telecentric Lenses are perfect for integration into gauging systems due to their excellent telecentricity and low distortion. The fixed iris and lockable focus make these lenses ideal for implementation into factory floors and assembly lines, as they will remain fixed over time.


Technical Information




#63-735, 3X, 65mm WD CompactTL™ Telecentric Lens, Distortion Plot




#63-735, 3X, 65mm WD CompactTL™ Telecentric Lens, Relative Illumination Plot



#63-735, 3X, 65mm WD CompactTL™ Telecentric Lens, Telecentricity Plot



#63-735, 3X, 65mm WD CompactTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 65mm Working Distance, f21.9



#63-735, 3X, 65mm WD CompactTL™ Telecentric Lens, Depth of Field Plot, 65mm Working Distance, f21.9