

## 4-10mm FL CS-Mount, DC Auto Iris, IR Corrected Lens



Image represents #22-799: Design will vary by stock number.

Stock **#22-799** **1 In Stock**

-

1

+

₹36,270

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹36,270 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**Note:** This item requires accessories for use | [Learn More](#)

Product Downloads

### SPECIFICATIONS

#### General

Varifocal Lens

Type:

#### Physical & Mechanical Properties

|                       |                                               |
|-----------------------|-----------------------------------------------|
| DC Auto Iris          | Iris Option:                                  |
| 51.50                 | Length (mm):                                  |
| 59.0                  | Maximum Diameter (mm):                        |
| 78                    | Weight (g):                                   |
| Optical Properties    |                                               |
| 112° - 44°            | Horizontal Field of View @ Max Sensor Format: |
| 4-10                  | Focal Length Range (mm):                      |
| 500 - ∞               | Working Distance (mm):                        |
| f/1.4 - Closed        | Aperture (f/#):                               |
| VS                    | Lens Wavelength Range:                        |
| Sensor                |                                               |
| 1/1.7"                | Maximum Sensor Format:                        |
| Threading & Mounting  |                                               |
| CS-Mount              | Mount:                                        |
| Regulatory Compliance |                                               |
| <a href="#">View</a>  | Certificate of Conformance:                   |

## PRODUCT DETAILS

- 4 - 10mm Focal Length Range for up to 135° Horizontal FOV
- True 4K, 12 Megapixel Resolution
- IR corrected for Day or Night

4K Wide Angle Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing for excellent resolution up to 12 megapixels. Available with DC auto-iris, P-iris, and manual iris versions, these lenses are ideal for a wide range of applications including Intelligent Traffic (ITS), remote sensing, security, and robotics. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination without manual adjustment. Lens mounting options include S-mount (M12), CS-mount, and C-mount with motorized and non-motorized versions available.