

[See all 11 Products in Family](#)

400mW 640nm OBIS XT

See More by [Coherent®](#)



Stock #75-323 NEW CONTACT US

-
1
+
MRP ₹18,54,252

● Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹18,54,252 each
Need More?	Request Quote

Product Downloads

General

	Warm-Up Time (minutes):
<5	
	Manufacturer:
Coherent®	
	Type of Laser:
Diode Pumped Solid State	
	Laser Class - CDRH:
IV	
	Model Number:
1443426	

Physical & Mechanical Properties

125.0 x 70.0 x 36.5	Dimensions (mm):
450	Weight (g):
<5	Pointing Stability ($\mu\text{rad}/^\circ\text{C}$):
<30	Pointing Stability (μrad):

Optical Properties

100:1	Polarization:
TEM ₀₀	Spatial Mode:
639.50	Wavelength (nm):
≤ 1.1	Mode Quality, M²:
± 0.05	Beam Diameter Tolerance (mm):
0.7	Beam Diameter (mm):
Full-Angle: <1.4	Beam Divergence (mrad):
Red	Color:

Electrical

400	Output Power (mW):
$\leq 0.25\%$ (20Hz to 20MHz)	RMS Noise:

Hardware & Interface Connectivity

Free Space	Output Type:
------------	---------------------

Environmental & Durability Factors

+10 to +35	Operating Temperature ($^\circ\text{C}$):
------------	---

Regulatory Compliance

View	Certificate of Conformance:
Germany	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Compact, Thermally Efficient Design for Ease of Life Science System Integration
- 320, 349, and 640nm Wavelength Options Available
- Integrated Controller with RS-232, RS-485, and USB Interfaces

Coherent OBIS XT Laser Systems offer an advanced extension of the [OBIS LS/LX](#), delivering powerful performance across ultraviolet and visible wavelengths. These lasers are available in UV wavelengths of 320 and 349nm, with output power options ranging from 20 to 150mW, and a higher-power 640nm wavelength option with output powers of 400 or 500mW. Flexible communication interfaces, including RS-232, RS-485, and USB, allow for seamless integration and real-time control in complex applications. Coherent OBIS XT Laser Systems are designed to simplify system integration, utilizing their compact form factor, integrated controller, as well as a low thermal output. This reduces the need for external cooling and streamlines OEM and end-user implementation. OBIS XT lasers are ideal for a wide range of applications, including life sciences, biomedical, flow cytometry, DNA Sequencing, and fluorescence microscopy.