


[See all 3 Products in Family](#)

LightPath 357786 | 2mm Dia., 0.50 NA, BBAR (350-600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock #37-108 **20+ In Stock**

⊖ 1 ⊕ ₹8,235

ADD TO CART

Volume Pricing	
Qty 1-10	₹8,235 each
Qty 11-49	₹7,245 each
Need More?	Request Quote

Product Downloads

General

357786 **Lightpath Lens Code:**

Aspheric Lens **Type:**

Physical & Mechanical Properties

Diameter (mm):

2.00 ±0.015

Clear Aperture CA (mm):

1.52

Edge Thickness ET (mm):

0.19

Center Thickness CT (mm):

0.50 ±0.05

Bevel:

Protective as needed

Optical Properties

Effective Focal Length EFL (mm):

1.41 @488nm

Numerical Aperture NA:

0.50

Substrate:

[D-Lak6](#)

Aspheric Design Wavelength (nm):

488

Coating:

BBAR (350-600nm)

Coating Specification:

R_{abs} <1.0% @ 350 - 600nm

Surface Quality:

40-20

f/#:

0.71

Wavelength Range (nm):

350 - 600

Working Distance (mm):

1.2

Conjugate Distance:

Infinite

Transmitted Wavefront Error (λ, RMS):

< 0.07

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Compliant](#)

Country of Origin:

China

Imported By:

Edmund Optics India Private Limited

Product Details

- Designs Optimized for 405nm and 488nm Laser Diodes
- Ideal for Biomedical Instrumentation and Data Storage Applications
- Diffraction Limited Molded Aspheric Lens Designs

LightPath® Blue Laser Collimating Aspheric Lenses are designed to simplify the design and implementation of laser systems for biomedical instrumentation. Ideal applications for this product include flow and imaging cytometers, fluorescence detection, and high-volume data storage systems. These aspheric lenses are designed and manufactured to meet stringent optical standards for the aforementioned high-performance applications. LightPath® Blue Laser Collimating Aspheric Lenses are delivered with a high-performance anti-reflection coating to provide optimum transmission in the 350 – 500nm wavelength range. These lenses are offered in a 2.0, 2.75, 4.0, and 6.33mm diameters in a range of EFL measurements.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)