

[See all 18 Products in Family](#)

TECHSPEC® 40mm, 60mm Radius, Metric Goniometer



TECHSPEC® Goniometers



Stock #66-529 **1 In Stock**

⊖ 1 ⊕ MRP ₹55,490

ⓘ Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-2	₹55,490 each
Qty 3+	₹48,438 each
Need More?	Request Quote

Product Downloads

General

Metric Type:

5 Resolution (arcmin):

Physical & Mechanical Properties

Goniometer	Type of Movement:
40 x 40	Stage Size (mm):
±10	Travel (°):
Brass Stage	Construction:
0.5	Leadscrew Pitch (mm):
3	Load Capacity (kg):
60	Radius R (mm):
1.57 x 1.57	Stage Size (inches):
0.3	Weight (kg):

Hardware & Interface Connectivity

Lead Screw	Type of Drive:
------------	-----------------------

Threading & Mounting

(1) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4	Mounting Threads:
--	--------------------------

Regulatory Compliance

Compliant	RoHS 2015:
-----------	-------------------

View	Certificate of Conformance:
------	------------------------------------

Compliant	REACH 241:
-----------	-------------------

Japan	Country of Origin:
-------	---------------------------

Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000	Imported By:
--	---------------------

Product Details


[Bottom adapter plates](#), sold separately, are required to mount 30mm and 40mm stages to standard breadboards.

- Metric and English Hole Patterns Available
- Stackable for Two-Axis Rotation
- Mechanically Compatible with our [TECHSPEC® Stages](#)

TECHSPEC® Goniometers allow for precise angular adjustment of an object about a fixed point located above the center of the mounting surface. They provide true tip and tilt adjustment of any optical component and are often used to accurately direct lasers and align mirrors in beam steering applications. These goniometers are available in with Metric and English hole patterns. TECHSPEC® Goniometers are available in different plate sizes to accommodate a host of applications. Each size is offered in several radii of movement for easily stacking into two axis configurations. To provide motion about a common point in two different axes, mount goniometer stages with smaller radii on top of those with larger radii of the same stage size.

Each goniometer stage features precision movement along a dovetail design with a vernier scale for high-resolution measurements and movement repeatability. A locking thumbscrew allows each to be held securely in place. 30mm and 40mm goniometer stages are constructed of durable black painted brass, while 70mm goniometer stages are constructed of black anodized aluminum. [Bottom adapter plates](#), sold separately, are required to mount 30mm and 40mm stages to standard breadboards; 70mm stages will mount directly.

Technical Information



		Top Stage																													
		30mm Linear Downtail	30mm Linear	30mm Vertical	30mm Tip/Tilt	30mm Goniometer	30mm Rotary	40mm Linear Downtail	40mm Linear	40mm Vertical	40mm Tip/Tilt	40mm Goniometer	40mm Rotary	65mm Linear Downtail	65mm Linear	65mm Vertical	65mm Tip/Tilt	65mm Goniometer	65mm Rotary	70mm Linear	70mm Vertical	70mm Tip/Tilt	70mm Goniometer	70mm Rotary	125mm Linear	125mm Vertical	125mm Tip/Tilt	125mm Rotary			
Bottom Stage	30mm Linear Downtail																														
	30mm Linear																														
	30mm Vertical																														
	30mm Tip/Tilt																														
	30mm Goniometer																														
	30mm Rotary																														
	40mm Linear Downtail																														
	40mm Linear																														
	40mm Vertical																														
	40mm Tip/Tilt																														
	40mm Goniometer																														
	40mm Rotary																														
	65mm Linear Downtail																														
	70mm Linear																														
	70mm Vertical																														
70mm Tip/Tilt																															
70mm Goniometer																															
70mm Rotary																															
125mm Linear																															
125mm Vertical																															
125mm Tip/Tilt																															
125mm Rotary																															

