

[See all 18 Products in Family](#)

**TECHSPEC® 4.0mm Diameter, Fused Silica Half-Ball Lens**



Stock #67-396 **20+ In Stock**

1 MRP ₹6,104

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹6,104 each
Qty 11-49	₹4,869 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Half-Ball Lens **Type:**

**Physical & Mechanical Properties**

4.00 **Diameter (mm):**

2.00 **Radius R (mm):**

**Radius Tolerance (µm):**

±2.5

Thickness Tolerance (µm):

±35

Diameter Tolerance (µm):

±2.5

## Optical Properties

**Fused Silica** (Coming 7980) **Substrate:**

Uncoated **Coating:**

200 - 2200 **Wavelength Range (nm):**

1.458 **Index of Refraction (n<sub>d</sub>):**

0.625 **Sphericity (µm):**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 247:**

Switzerland **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details


- Excellent UV Transmission
- Low Coefficient of Thermal Expansion
- Ball and Half-Ball Options Available

TECHSPEC® Fused Silica Ball and Half-Ball Lenses feature high transmission from 200nm to 2.2µm with a low coefficient of thermal expansion, making it ideal for the most demanding ball lens applications in the ultraviolet, visible, and near-infrared spectra. Ball lenses are commonly used for improving signal coupling between fibers, emitters, and detectors, as well as objective lenses in endoscopy and bar-code scanning applications. Half-ball lenses simplify handling and integration. TECHSPEC Fused Silica Ball and Half-Ball Lenses are uncoated with a fused silica substrate. The lenses are available in diameters ranging from 0.50 to 5.00mm.

## Technical Information



UV FS Transmission Curve



## Compatible Mounts

---