


## 445nm Monolithic Collimator



Monolithic Collimator

Stock **#29-412** **3 In Stock**

⊖ 1 ⊕ ₹7,707

**ADD TO CART**

### Volume Pricing

Qty 1-9	₹7,707 each
Qty 10-25	₹6,929 each
Qty 26-49	₹6,539 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Beam Shaping Lens **Type:**

### Physical & Mechanical Properties

1.90 x 1.90 **Clear Aperture CA (mm):**

2.50 x 2.50 ±0.05 **Dimensions (mm):**

5.78 ±0.05 **Thickness (mm):**

## Optical Properties

5.02 **Effective Focal Length EFL (mm):**

**Substrate:**   
[S-BSL7](#)

0.50 (Fast Axis)  
0.20 (Slow Axis) **Numerical Aperture NA:**

BBAR (400 - 700nm) **Coating:**

400 - 700 **Wavelength Range (nm):**

1.19 **Back Focal Length BFL (mm):**

445 **Design Wavelength DWL (nm):**

1.526 **Index of Refraction (n<sub>d</sub>):**

1.6 (Fast Axis, Typical)  
7.0 (Slow Axis, Typical) **Divergence 1/e<sup>2</sup> (mrad):**

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

Germany **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

## Product Details

- Simultaneously Collimate Light from Laser Diode Fast and Slow Axes
- Circularize Elliptical Output from Common Blue Laser Diodes
- Ideal for Light Collimation of Single Emitters in the Blue Spectrum

Monolithic Collimators feature a solid glass construction with two orthogonal cylindrical surfaces. The different focal lengths, optimized for numerical apertures of 0.5 and 0.2, simultaneously collimate light from the fast and slow axes of common single emitters. These collimators are capable of producing a symmetrical beam with a nearly round far-field profile. Monolithic Collimators are AR coated to provide high transmission across visible wavelengths and are ideal for beam shaping or laser diode collimation, particularly of blue TO-can diodes with wavelengths of 405nm, 445nm, 447nm, and 450nm.