

[See all 59 Products in Family](#)

44mm ID, 38.5mm Inner Length, IP67 C-Mount Lens Tube

See More by [LUCID Vision Labs™](#)



44mm ID IP67 C-Mount Lens Tube



Stock **#13-742** 5 In Stock

-

1

+

₹10,384

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹10,384 each
Need More?	Request Quote

Product Downloads

General	
Camera Accessory	Type:
IPTC-D440L385	Model Number:
38.5	Inner Length (mm):

Compatible with Lucid Vision Labs Triton™ camera models		Note:
Physical & Mechanical Properties		
49.0	Length (mm):	
51.0	Outer Diameter (mm):	
44.0	Inner Diameter (mm):	
Sensor		
Global	Shutter Type:	
Regulatory Compliance		
View	Certificate of Conformance:	
Japan	Country of Origin:	
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000		Imported By:

Product Details

- Compact 29 x 29 x 45mm Form Factor
 - Global, Rolling, or Polarized CMOS Sensors
 - IP67 Protection with Optional Lens Tubes
- LUCID Vision Labs Triton™ GigE Power over Ethernet (PoE) Cameras provide exceptional price performance in a compact 29 x 29mm form factor. These cameras are available with Sony's Pregius™ and Starvis™ imaging sensors with up to 24.5 megapixels of resolution, as well as Sony's polarized sensor. Each imaging sensor is actively aligned during manufacturing, ensuring sharp and crisp images even in the corners. Using the accessory IP67 lens tubes (sold separately), LUCID Vision Labs Triton GigE Power over Ethernet (PoE) Cameras can operate in harsh environments where dust or water are present up to IP67 thresholds. Triton cameras are ideal for automotive, process control, and food and beverage applications.