

[See all 2 Products in Family](#)

45° Full Fan Angle Laser Line Generator Lens



Powell Lenses

Stock **#43-474** CLEARANCE CONTACT US

1 MRP ₹26,736

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-5	₹26,736 each
Qty 6-25	₹22,096 each
Qty 26-49	₹21,389 each
Need More?	Request Quote

Product Downloads

General

Beam Shaping Lens **Type:**

Physical & Mechanical Properties

8.90 +0.00/-0.15 **Diameter (mm):**

Height (mm):

8.90 +0.00/-2.00

Optical Properties

N-SF6	Substrate: □
VIS-NIR (450-900nm)	Coating:
450 - 900	Wavelength Range (nm):
BBAR @450 - 900nm	Coating Specification:
1.805	Index of Refraction (n_d):
45.00	Fan Angle (°):


Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:
Thailand	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Ideal for Alignment and Machine Vision Applications
- Multiple Fan Angles Available
- Creates Uniform, Straight Line

Powell Lenses, also known as Laser Line Generator Lenses, are optimized for a 0.8mm diameter laser beam input. The VIS-NIR coated lenses convert laser beams into uniform, straight lines. Unlike cylindrical lenses, which generate Gaussian beam profiles with hot-spot center points and fading edges, Powell Lenses provide an even distribution of energy along the length of the entire line. Powell Lenses are ideal for alignment and machine vision applications. These lenses are offered with multiple fan angles and come in an 8.90mm diameter size.



Technical Information

