

[See all 20 Products in Family](#)

TECHSPEC® 45° AOI, 101 x 127mm, Hot Mirror



TECHSPEC High Performance Hot Mirrors

Stock **#64-472** [CONTACT US](#)

1 [-](#) [+](#) MRP ₹24,113

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹24,113 each
Qty 10-25	₹21,692 each
Qty 26-49	₹20,582 each
Need More?	Request Quote

Product Downloads

General

Dichroic Filter **Type:**

Physical & Mechanical Properties

3.30 ±0.2 **Thickness (mm):**

Dimensions (mm):

101.0 x 127.0

Dimensional Tolerance (mm):

+0.0/-0.2

Length (mm):

127.00

Width (mm):

101.00

Optical Properties

Coating Type:

Dielectric

Coating:

Hot Mirror, 45°

Surface Flatness (P-V):

4 - 6λ

Wavelength Range (nm):

400 - 1125

Substrate:

BOROFLOAT®

Angle of Incidence (°):

45

Coating Specification:

T_{avg} >85% @ 400 - 690nm, R_{avg} >95% @ 750 -

1125nm

AR: R_{avg} <1% @ 400 - 700nm

Surface Quality:

80-50

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

Country of Origin:

United States

Imported By:





Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- High Transmission from 400 - 690nm
- High Reflection from 750 - 1125nm
- Ideal for Minimizing Heat Build-Up

TECHSPEC® High Performance Hot Mirrors feature a multi-layer dielectric coating optimized for greater than 85% transmission of visible light and greater than 95% reflection of IR wavelengths. For high power illumination, forced air cooling is recommended. Hot mirrors, also known as heat-reflecting mirrors, are crucial in many projection and illumination systems where high levels of heat can quickly damage sensitive components. TECHSPEC High Performance Hot Mirrors are ideal for minimizing heat build-up. Hot mirrors are specially coated to transmit visible light while reflecting the NIR, a major contributor to heat generation. By using a hot mirror, heat levels are limited with minimum impact on the overall system performance.

Technical Information



Quote Your Size

Compatible Mounts
