

[See all 13 Products in Family](#)

# Coherent® VHK™ Circular Beam Visible Laser Diode 0221-700-01 | 4.9mW 635nm

See More by [Coherent®](#)



Coherent® VHK™ Circular Beam Visible Laser Diode

Stock #54-025 **15 In Stock**

MRP ₹74,340

**1** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹74,340 each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

## Product Downloads



## General

Diode **Type of Laser:**

IIIa **Laser Class - CDRH:**

## Physical & Mechanical Properties

**Pointing Accuracy (mrad):**

<4

0.580 **Diameter (inches):**

1.32 **Length (inches):**

## Optical Properties

635.00 **Wavelength (nm):**

1.1 @ module face **Beam Diameter (mm):**

0.70 **Beam Divergence (mrad):**

Red **Color:**

## Electrical

4.9 **Output Power (mW):**

60/70 (Typical/Maximum) **Current (mA):**

## Hardware & Interface Connectivity

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#59-099](#)  
Europe: [#35-201](#)  
Japan: [#59-099](#)  
Korea: [#33-771](#)  
China: [#59-099](#)

5-10V DC **Power Requirement:**

red (+), black (-), case (+) **Electrical Leads/ Pin Connections:**

Free Space **Output Type:**

5-10 DC **Input Voltage (V):**

## Environmental & Durability Factors

-10 to +40 **Operating Temperature (°C):**

-40 to +80 **Storage Temperature (°C):**

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

Thailand **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Robust, High Quality Laser Diodes with Small Form Factor
- 635nm and 670nm High Visibility Wavelengths
- Sophisticated Electronic Design for Consistent Beam Properties


Coherent® Visible Laser Diode Modules feature a compact form factor to help users achieve space saving designs in systems that require a collimated light source. The simple design of these laser diodes allows for quick and efficient incorporation into a wide array of optical systems. A sophisticated electronic design aids in producing consistent laser power and beams. Coherent® Visible Laser Diode Modules with advanced AlignLock™ optical assembly technology provide a remarkable beam-pointing alignment of <4.3mrad, making these laser diodes a great choice for precision applications. These robust, compact laser diodes are typically used in machine vision, medical equipment, and many other industrial applications.

**Note:** [Power Supply](#), sold separately, is required for operation.

## Technical Information



VLM™ High Quality Laser Diode Module - Micro Series



VLM™ High Quality Laser Diode Modules