

5 x 5mm, 600 - 1100nm, Corning Polarcor™ Glass Polarizer



Corning Polarcor™ Glass Polarizers

Stock **#13-628** **1 In Stock**

MRP ₹16,647

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹16,647 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Length (mm):
5.00

Dimensions (mm):
5.0x5.0

Thickness (mm):
0.50 ±0.05

Dimensional Tolerance (mm):
±0.1

Width (mm):

5.00

Knoop Hardness (kg/mm²):

480.00

Young's Modulus (GPa):

58.605

Poisson's Ratio:

0.21

Optical Properties

Angle of Incidence (°):

0 ±5

Coating:

BBAR (600-1100nm)

Extinction Ratio:

>10,000:1

Substrate:

Borosilicate Glass Containing Elongated Silver Crystals

Minimum Transmission (%):

>66

Surface Quality:

40-20

Coating Specification:

R_{avg} <1.0% @ 600 - 1100nm

Wavelength Range (nm):

600 - 1100

Index of Refraction (n_d):

1.5218-1.5107

Abbe Number (v_d):

57.6

Hardware & Interface Connectivity

Insertion Loss (dB):

<1.8

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

6.5

Density (g/cm³):

2.412

Regulatory Compliance

RoHS 2015:

Compliant

Reach 224:

Compliant

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- High Extinction Ratio and Low Insertion Loss in the NIR
- Resistant to Chemical, Physical, and Thermal Damage
- Suitable for High Power Applications
- Range of Standard Sizes and Custom Options Available

Corning Polarcor™ Glass Polarizers feature a high extinction ratio and low insertion loss at wavelengths in the NIR. These linear polarizers consist of elongated silver crystals aligned within a borosilicate glass substrate, providing a

polarization mechanism based on resonant absorption. This polarization mechanism causes light of unwanted polarization directions to be absorbed, ensuring that stray light is eliminated. Coming Polarcor™ Glass Polarizers can be used to polarize light, block polarized light, reduce reflections, improve image contrast, modulate and control the intensity of light, or improve the signal to noise ratio. These polarizers are ideal for integration into polarization-dependent optical isolators, optical modulators, and other polarization-based devices in the telecommunications, medical, and defense industries.
