


5 x 5mm, 800nm, Corning Polarcor™ Glass Polarizer



Corning Polarcor™ Glass Polarizers

Stock #13-616 **7 In Stock**

MRP ₹16,647

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹16,647 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Length (mm):
5.00

Dimensions (mm):
5.0 x 5.0

Thickness (mm):
0.50 ± 0.05

Dimensional Tolerance (mm):
± 0.1

Width (mm):

5.00	Knoop Hardness (kg/mm²):
480.00	
	Young's Modulus (GPa):
58.605	
	Poisson's Ratio:
0.21	

Optical Properties

	Angle of Incidence (°):
0 ±5	
	Coating:
BBAR (740-860nm)	
	Design Wavelength DWL (nm):
800	
	Extinction Ratio:
>10,000:1	
	Substrate: <input type="checkbox"/>
Borosilicate Glass Containing Elongated Silver Crystals	
	Minimum Transmission (%):
>91.3	
	Surface Quality:
40-20	
	Coating Specification:
R _{avg} <0.4% @ 740 - 860nm	
	Wavelength Range (nm):
740 - 860	
	Index of Refraction (n_d):
1.5161	
	Abbe Number (v_d):
57.6	

Hardware & Interface Connectivity

	Insertion Loss (dB):
<0.39	

Material Properties

	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
6.5	
	Density (g/cm³):
2.412	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Reach 224:
Compliant	
	Certificate of Conformance:
View	
	Country of Origin:
United States	
	Imported By:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- High Extinction Ratio and Low Insertion Loss in the NIR

- Resistant to Chemical, Physical, and Thermal Damage
- Suitable for High Power Applications
- Range of Standard Sizes and Custom Options Available

Corning Polarcor™ Glass Polarizers feature a high extinction ratio and low insertion loss at wavelengths in the NIR. These linear polarizers consist of elongated silver crystals aligned within a borosilicate glass substrate, providing a polarization mechanism based on resonant absorption. This polarization mechanism causes light of unwanted polarization directions to be absorbed, ensuring that stray light is eliminated. Corning Polarcor™ Glass Polarizers can be used to polarize light, block polarized light, reduce reflections, improve image contrast, modulate and control the intensity of light, or improve the signal to noise ratio. These polarizers are ideal for integration into polarization-dependent optical isolators, optical modulators, and other polarization-based devices in the telecommunications, medical, and defense industries.
