

[See all 8 Products in Family](#)

## 50 x 50mm, 7-15 $\mu$ m, High Contrast IR Wire Grid Polarizer



Stock **#88-250** **5 In Stock**

1  MRP ₹2,44,659

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹2,44,659 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Linear Polarizer **Type:**

#### Physical & Mechanical Properties

50.00 **Length (mm):**

50.0 x 50.0  $\pm$  0.4 **Dimensions (mm):**

0.70  $\pm$  0.07 **Thickness (mm):**

Wire Grid	<b>Construction:</b>
±2	<b>Alignment Tolerance (°):</b>
50.00	<b>Width (mm):</b>
Aluminum	<b>Microwire Material:</b>
<b>Optical Properties</b>	
0 ±20	<b>Angle of Incidence (°):</b>
7000:1 @ 8µm, 7000:1 @ 10.6µm, 7000:1 @ 12µm	<b>Extinction Ratio:</b>
Silicon (Si)	<b>Substrate:</b> <input type="checkbox"/>
T <sub>p</sub> >85% @ 8.0µm T <sub>p</sub> >81% @ 10.6µm T <sub>p</sub> >75% @ 12.0µm	<b>Transmission (%):</b>
8000 - 12000	<b>Wavelength Range (nm):</b>
100 kW/cm <sup>2</sup> Blocking Direction 10 kW/cm <sup>2</sup> Transmission Direction @ 3.3µm, 7ns, 25kHz, 150µm Spot Size	<b>Damage Threshold, By Design:</b> <input type="checkbox"/>
<b>Material Properties</b>	
2.6 x 10 <sup>-7</sup> /°C	<b>Thermal Expansion:</b>
<b>Environmental &amp; Durability Factors</b>	
Up to 200	<b>Operating Temperature (°C):</b>
<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">Compliant</a>	<b>Reach 224:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

Due to the wire grid being exposed, special care should be taken when handling to prevent damage to the polarizer.

- AR Coated for Superior Transmission
- High Heat Resistance with Low Thermal Expansion
- Feature Wide Angle of Incidence Range without Performance Loss

High Contrast IR Wire Grid Polarizers are ideal for broadband infrared applications that require high transmission and contrast, including spectroscopy, remote sensing, thermal imaging, or astronomy. Aluminum Microwire versions consist of a silicon substrate and are available in both 3-5µm and 7-12µm options. These polarizers will have up to 7000:1 contrast at their specified wavelengths, and a temperature resistance of up to 200°C. Gold Microwire versions consist of a silicon substrate with gold microwires and feature superior contrast of at least 10,000:1 @ 3.4µm. Due to their unique construction, these polarizers have a substantial temperature resistance of up to 500°C making them perfect even for the most demanding applications. High Contrast IR Wire Grid Polarizers allow the angle of incidence to vary from ±20° for the aluminum microwire versions or ±25° for the gold without displaying performance loss.

**Note:** Due to the exposed wire grid, special care should be taken when handling to prevent damage to the polarizer. The wire grid surface should never be touched directly, and parts should be handled by the edges only, with light pressure, using gloves. The glass side can be gently cleaned using isopropyl alcohol, but the wire grid side should only be cleaned using compressed air.

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

## Compatible Mounts

---

;