

[See all 12 Products in Family](#)

50 x 50mm UV Fused Silica Ground Glass Optical Diffuser



Stock **#49-159** [CONTACT US](#)

- 1 + MRP ₹11,603

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹11,603 each
Qty 11-49	₹9,182 each
Need More?	Request Quote

Product Downloads

General

Ground Glass Diffuser **Type:**

Physical & Mechanical Properties

50.00 x 50.00 **Dimensions (mm):**

220 **Grit:**

Thickness (mm):

1.60

50.00

Width (mm):

50.00

Length (mm):

Optical Properties

Fused Silica (Corning 7980)

Substrate:

200 - 2200

Wavelength Range (nm):

Regulatory Compliance

Compliant

RoHS 2015:

Compliant

Reach 219:

[View](#)

Certificate of Conformance:

United States

Country of Origin:

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Even, Diffuse Surface
- Ideal for Applications Utilizing UV Wavelengths
- Low Scatter Loss
- [Float Glass Substrates](#) Also Available

UV Fused Silica Ground Glass Diffusers are comprised of high tolerance, quality ground glass, making them ideal for a variety of industrial applications. A 220-grit sandblast is used to create a diffuse surface on the UV fused silica substrate of these optical diffusers. Undergoing two orthogonal passes during this sandblast process yields an even diffusion across the surface. The scattering is a compromise of low scatter loss and medium diffusion. UV Fused Silica Ground Glass Diffusers are typically applied for use in screens, illuminator diffusion, and targets.

Technical Information



Compatible Mounts