

[See all 5 Products in Family](#)

50.0/50.8mm Optic Dia., Low Wavefront Distortion Kinematic Mount, 2-Screws



Stock #28-748 [CONTACT US](#)

- 1 + ₹27,264

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹27,264 each
Need More?	Request Quote

Product Downloads

General

Circular **Type of Optics:**

2XRear **Number of Adjustment Screws:**

Physical & Mechanical Properties

47.8 **Clear Aperture CA (mm):**

Brass Plates and Stainless Steel Screws **Construction:**

Optical Axis Height (mm):

38.10

Threading & Mounting

Size of Compatible Optics (mm):

50.00 - 50.80

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Low Wavefront Distortion Mounting
- Lockable 100 TPI Fine Adjustment Screws for High Precision and Long-Term Stability
- Space Efficient Rear Adjustment and Top Adjustment Versions

Ultraprecision Kinematic Mounts are designed to provide precise and accurate adjustment of high-end optical components, offering long-term pointing stability and minimizing wavefront distortion. The optic is located in the mounting seat via three contact points, but is secured in place by a retaining spring that gently contacts the leading edge of the optic at three discrete locations to ensure low wavefront distortion, preserving optical flatness and accuracy. These kinematic mounts feature two hex-driven high accuracy adjustment screws (100TPI), that can be easily locked, ensuring long term stability under shock, vibration, and gradient temperature conditions. Ultraprecision Kinematic Mounts are compact in footprint and are available in both standard rear- and top-adjustment configurations, with the top adjust versions being extra space efficient for compact system integration. These mounts are highly configurable, featuring multiple counterbore holes, threaded holes, and dowel pin holes for locating and securing the mounts in any benchtop or OEM application.

Technical Information

