

[See all 46 Products in Family](#)

50.8mm Dia, 340 - 560nm, $\lambda/2$ Achromatic Waveplate



Achromatic Waveplates (Retarders)

Stock **#39-029** **1 In Stock**

⊖ 1 ⊕ MRP ₹3,52,611

● Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | ₹3,52,611 each |
| Qty 6+ | ₹3,05,193 each |
| Need More? | Request Quote |

Product Downloads

General

Achromatic Waveplate **Type:**

Air Spaced **Configuration:**

Physical & Mechanical Properties

>34.0 **Clear Aperture CA (mm):**

| | |
|-------------|------------------------------------|
| 50.80 | Diameter (mm): |
| 6.00 ±0.2 | Thickness (mm): |
| +0/-0.25 | Dimensional Tolerance (mm): |
| Crystalline | Construction: |
| <10 | Parallelism (arcsec): |
| +0/-0.25 | Housing Tolerance (mm): |

Optical Properties

| | |
|---|--|
| R _{avg} <0.75% @ 340 - 560nm | Coating: |
| Crystal Quartz and MgF ₂ | Substrate: <input type="checkbox"/> |
| λ/2 | Retardance: |
| 40-20 | Surface Quality: |
| <λ/4 @ 632nm | Transmitted Wavefront, P-V: |
| λ/100 @ 20°C | Retardance Tolerance: |
| R _{avg} <0.75% @ 340 - 560nm | Coating Specification: |
| 340 - 560 | Wavelength Range (nm): |
| >5 J/cm ² @ 1064nm, 10ns, 10Hz | Damage Threshold, By Design: <input type="checkbox"/> |

Regulatory Compliance

| | |
|---|------------------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 247: |
| Lithuania | Country of Origin: |
| Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000 | Imported By: |


Product Details

- Multiple Wavelength Ranges Available
- Flat Response Over Each Broad Spectral Range
- λ/4 and λ/2 Retardance
- Mounted in Black Anodized Aluminum Housing

Achromatic Waveplates (Retarders) provide a constant phase shift independent of the wavelength of light that is used. This wavelength independence is achieved by using two different birefringent crystalline materials. The relative shifts in retardation over the wavelength range are balanced between the two materials used. Achromatic Waveplates (Retarders), with their flat response, are ideal for use with tunable lasers, multiple laser line systems, and other broad-spectrum sources.


Designed to be used at an angle of incidence of 0°, changes of ±3° will yield less than 1% change in retardance. The 23mm clear aperture waveplates will feature a cemented construction. All Achromatic Waveplates (Retarders) are mounted in an anodized aluminum housing with the fast axis clearly indicated.

Technical Information





25.4mm Diameter Waveplates



30.0mm Diameter Waveplates

