

[See all 4 Products in Family](#)

50.8mm Dia., 3mm Thick, Uncoated, ISP Optics Magnesium Fluoride (MgF₂) Window | MF-W-50-3

See More by [ISP Optics](#)



Stock #24-486 CLEARANCE **4 In Stock**

1 MRP ₹44,897

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹44,897 each
Need More?	Request Quote

Product Downloads

General

MF-W-50-3	Model Number:
Protective Window	Type:
Crystal	Type of Window:

Physical & Mechanical Properties

43.18	Clear Aperture CA (mm):
50.80 +0.00/-0.13	Diameter (mm):
3.00 ±0.13	Thickness (mm):
<3	Parallelism (arcmin):
Protective as needed	Bevel:
85	Clear Aperture (%):
Fine Ground	Edges:
0.27	Poisson's Ratio:
138	Young's Modulus (GPa):
415.00	Knoop Hardness (kg/mm²):

Optical Properties

Uncoated	Coating:
Magnesium Fluoride (MgF ₂)	Substrate: <input type="checkbox"/>
1.377	Index of Refraction (n_d):
40-20	Surface Quality:
106.22	Abbe Number (v_d):
120 - 7000	Wavelength Range (nm):
2λ	Surface Flatness (P-V):

Material Properties

3.18	Density (g/cm³):
13.7	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
Latvia	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Excellent Transmission from 0.12 to 7µm
- Rugged and Durable
- Resistant to Chemical Etching

ISP Optics Magnesium Fluoride (MgF₂) Windows feature a low refractive index and high transmission from the Deep UV (DUV) to the Mid-Wave Infrared (MMR), without the need for an Anti-Reflection (AR) coating. Magnesium Fluoride is extremely durable, being resistant to mechanical and thermal shock. Featuring strong resistance to chemical etching and stability in water, these windows are able to be used in harsh external environments. ISP Optics Magnesium Fluoride (MgF₂) Windows are ideal for a wide range of applications from use in the DUV for Hydrogen Lyman-alpha line applications and excimer laser applications, to applications requiring transparency across multiple wavelengths such as spectroscopy and fluorescence imaging.