

50.8mm Dia., 3mm Thick, Uncoated, ISP Optics Thallium Bromoiodide (KRS-5) Window | K5-W-50-3

See More by [ISP Optics](#)



Thallium Bromoiodide (KRS-5) Windows

Stock **#16-803** CLEARANCE **2 In Stock**

-

1

+

₹1,67,605

ADD TO CART

Volume Pricing	
Qty 1+	₹1,67,605 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Protective Window

Type:

Model Number:

K5-W-50-3	
Physical & Mechanical Properties	
Protective as needed	Bevel:
85	Clear Aperture (%):
43.18	Clear Aperture CA (mm):
50.80 +0.00/-0.13	Diameter (mm):
3.00 ±0.13	Thickness (mm):
Fine Ground	Edges:
40.20	Knoop Hardness (kg/mm²):
<3	Parallelism (arcmin):
0.37	Poisson's Ratio:
31	Young's Modulus (GPa):
Optical Properties	
Uncoated	Coating:
2.45 @ 1µm 2.38 @ 4µm 2.37 @ 10µm 2.21 @ 40µm	Index of Refraction (n _d):
Thallium Bromiodide (KRS-5)	Substrate:
N10 @ 10.6µm	Surface Flatness (P-V):
60-40	Surface Quality:
700 - 40000	Wavelength Range (nm):
Material Properties	
6.0	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
7.37	Density (g/cm³):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:


PRODUCT DETAILS

- Broad Transmission from 700nm - 40µm
- Non-Hydroscopic
- Ideal for FTIR Spectroscopy with Aqueous Samples

ISP Optics Thallium Bromiodide (KRS-5) Windows provide flat transmission across the broad wavelength range of 700nm - 40µm. KRS-5 is non-hygroscopic and relatively insoluble in water, allowing for its use in FTIR spectroscopy as liquid cell windows for the analysis of aqueous samples. These windows also have good chemical resistance except against strong acids. ISP Optics Thallium Bromiododide (KRS-5) Windows are ideal for use in FTIR spectroscopy, as protective windows for acid-sensitive or hygroscopic optics, or as substrates for infrared holographic polarizers.

Note: Thallium bromiodide (KRS-5) is a toxic material that can be absorbed through the skin. Gloves must be worn while handling this material. KRS-5 has a tendency to cold flow and the shape of these optics may change over time.

TECHNICAL INFORMATION



SPECIAL HANDLING

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools