

50.8mm Dia, 900 - 2100nm, $\lambda/2$ Achromatic Waveplate



Achromatic Waveplates (Retarders)

Stock **#39-053** 1 In Stock

-

1

+

₹2,50,288

ADD TO CART

Volume Pricing	
Qty 1-5	₹2,50,288 each
Qty 6+	₹2,16,890 each
Need More?	Request Quote

Product Downloads

General	
Achromatic Waveplate	Type:
Air Spaced	Configuration:
Physical & Mechanical Properties	
>34.0	Clear Aperture CA (mm):
	Diameter (mm):

50.80	
6.00 ±0.2	Thickness (mm):
+0/-0.25	Dimensional Tolerance (mm):
Crystalline	Construction:
<10	Parallelism (arcsec):
+0/-0.25	Housing Tolerance (mm):

Optical Properties	
R _{avg} <0.75% @ 900 - 2100nm	Coating:
Crystal Quartz and MgF ₂	Substrate: □
<i>N</i> /2	Retardance:
40-20	Surface Quality:
< <i>N</i> /4 @ 632nm	Transmitted Wavefront, P-V:
<i>N</i> /100 @ 20°C	Retardance Tolerance:
R _{avg} <0.75% @ 900 - 2100nm	Coating Specification:
900 - 2100	Wavelength Range (nm):
>5 J/cm ² @ 1064nm, 10ns, 10Hz	Damage Threshold, By Design: □

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
Lithuania	Country of Origin:
Edmund Optics India Private Limited	Imported By:


Product Details


- Multiple Wavelength Ranges Available
- Flat Response Over Each Broad Spectral Range
- *N*/4 and *N*/2 Retardance
- Mounted in Black Anodized Aluminum Housing

Achromatic Waveplates (Retarders) provide a constant phase shift independent of the wavelength of light that is used. This wavelength independence is achieved by using two different birefringent crystalline materials. The relative shifts in retardation over the wavelength range are balanced between the two materials used. Achromatic Waveplates (Retarders), with their flat response, are ideal for use with tunable lasers, multiple laser line systems, and other broad-spectrum sources.






Designed to be used at an angle of incidence of 0°, changes of ±3° will yield less than 1% change in retardance. The 23mm clear aperture waveplates will feature a cemented construction. All Achromatic Waveplates (Retarders) are mounted in an anodized aluminum housing with the fast axis clearly indicated.

Technical Information





25.4mm Diameter Waveplates



30.0mm Diameter Waveplates

