

[See all 16 Products in Family](#)

**TECHSPEC®**

**50.8mm Dia. x 190.6mm EFL, 800-1150nm Ultrafast-Enhanced Silver Coated, 50Å OAP Mirror**



TECHSPEC® Ultrafast-Enhanced Silver Coated Off-Axis Parabolic (OAP) Mirrors

Stock **#25-605** **10 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ MRP ₹60,130

**1** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹60,130 each
Qty 6-10	₹48,125 each
Qty 11-25	₹45,098 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Off-Axis Parabolic Mirror **Type:**

**Physical & Mechanical Properties**

190.60	<b>Y Offset (mm):</b>
50.80	<b>Diameter (mm):</b>
<50 RMS	<b>Surface Roughness (□):</b>

## Optical Properties

Ultrafast-Enhanced Silver	<b>Coating Type:</b>
Ultrafast-Enhanced Silver (800 - 1150nm)	<b>Coating:</b>
90	<b>Off-Set Angle (°):</b>
800 - 1150	<b>Wavelength Range (nm):</b>
190.60	<b>Effective Focal Length EFL (mm):</b>
Aluminum 6061-T6	<b>Substrate:</b> □
<b>Coating Specification:</b> R <sub>avg</sub> >99% @ 800 - 1150nm, 0° R <sub>s</sub> >99% @ 800 - 1100nm, 45° R <sub>p</sub> >98.5% @ ~850 - 1100nm, 45°	
±1	<b>Focal Length Tolerance (%):</b>
95.30	<b>Parent Focal Length PFL (mm):</b>
λ/8	<b>Surface Figure, RMS:</b>
80-50	<b>Surface Quality:</b>
<b>Damage Threshold, Reference:</b> □ 0.35 J/cm <sup>2</sup> @ 1030nm, 200fs, 1 pulse (typical) 0.10 J/cm <sup>2</sup> @ 1030nm, 200fs, 100Hz, 1000 pulses (typical)	
0 ±30fs <sup>2</sup> @ 800 - 1100nm	<b>GDD Specification:</b>
190.60	<b>Radius of Curvature (mm):</b>
λ/4	<b>Reflected Wavefront, RMS:</b>

## Threading & Mounting

#47-112	<b>Compatible Mounting Plates:</b>
---------	------------------------------------

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


## Product Details

- Ultrafast-Enhanced Silver Coating for Ti:sapphire and Yb:doped Lasers
- Low Group Delay Dispersion
- <50Å RMS Surface Roughness to Minimize Scatter

TECHSPEC® Ultrafast-Enhanced Silver Coated Off-Axis Parabolic (OAP) Mirrors are used to collimate or focus incident light at a specified offset angle. These mirrors are coated with an ultrafast-enhanced silver coatings which

provide a >99% reflectivity while maintaining a low group delay dispersion (GDD) of  $0 \pm 20\text{fs}^2$  at their design wavelength range. The off-axis design of these mirrors separates the focal point from the beam path, allowing for more interactive space around the focal point without disrupting the incident beam. TECHSPEC Ultrafast-Enhanced Silver Coated OAP Mirrors are ideal for focusing laser light from low-to-medium power ultrafast lasers, including Ti:sapphire and Yb:doped fiber lasers, while minimizing the temporal spreading of the ultrafast pulses. Mounting plates with holes perpendicular to the optical axis are available for mounting these mirrors into benchtop systems.

## Technical Information



600-1000nm Ultrafast-Enhanced Silver

;