

[See all 12 Products in Family](#)

TECHSPEC[®] 50mm Dia., VIS Coated, Linear Glass Polarizer (XP42)



Stock **#19-652** 5 In Stock

-

1

+

₹14,169

ADD TO CART

Volume Pricing	
Qty 1-9	₹14,169 each
Qty 10+	₹12,767 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer

Type:

Physical & Mechanical Properties

50.00

Diameter (mm):

2.00 ±0.10

Thickness (mm):

+0.00/-0.20

Dimensional Tolerance (mm):

Laminated Glass Polarizing Film		Construction:
Optical Properties		
VIS AR Coated		Coating:
9000:1 @ 546nm		Extinction Ratio:
XP42 Laminated Between Glass		Substrate: □
45 @ 546nm		Transmission (%):
Ravg <0.5% @ 425 - 700nm		Coating Specification:
425 - 700		Wavelength Range (nm):
>99.98 @ 546nm		Polarization Efficiency (%):
Environmental & Durability Factors		
-10 to +55		Operating Temperature (°C):
Regulatory Compliance		
Compliant		RoHS 2015:
View		Certificate of Conformance:
Compliant		Reach 235:
Japan		Country of Origin:
Edmund Optics India Private Limited		Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Uncoated and Visible AR Coated Options
- >99.98% Polarization Efficiency
- 42% Transmission for Uncoated and 45% Transmission for AR Coated Versions
- XP42 [Plastic](#) and [Film](#) Also Available

TECHSPEC® High Contrast Glass Linear Polarizers (XP42) are a high transmission, high efficiency solution that are ideal for a broad range of industrial and laboratory applications. Featuring a >99.98% polarization efficiency and an extinction ratio of 9000:1, these polarizers are constructed with an [XP42 high contrast linear polarizing film](#) laminated between two pieces of optical grade glass. TECHSPEC High Contrast Glass Linear Polarizers (XP42) are available uncoated or with a visible AR coating that provides increased transmission from 425 – 700nm. Typical single filter transmission with randomly polarized incident light is 42% for the uncoated options and 45% for the AR coated options.