

TECHSPEC[®] 50mm Dia. x 3mm Thick, 8-12μm AR Coated & DLC Coated, Ge Window



TECHSPEC[®] Diamond-Like Carbon (DLC) Coated Germanium Windows

Stock **#13-798** CLEARANCE CONTACT US

-

1

+

₹1,44,420

ADD TO CART

Volume Pricing	
Qty 1+	₹1,44,420 each
Need More?	Request Quote

Product Downloads

General	
Protective Window	Type:
Arrow on substrate edge points towards DLC coated surface	Note:
Physical & Mechanical Properties	
Protective as needed	Bevel:
90	Clear Aperture (%):

45.00	Clear Aperture CA (mm):
50.00 +0.0/-0.1	Diameter (mm):
3.00 ±0.1	Thickness (mm):
Fine Ground	Edges:
780.00	Knoop Hardness (kg/mm²):
<1	Parallelism (arcmin):

Optical Properties	
S1: DLC Coating S2: BBAR (8000-12000nm)	Coating:
AR: R _{avg} ≤0.5% @ 8000 - 12000nm	Coating Specification:
Germanium (Ge)	Substrate:
60-40	Surface Quality:
8000 - 12000	Wavelength Range (nm):
AR: -80 to +160 per MIL-C-48497A Paragraph 4.5.4.1 DLC: -80 to +160 per MIL-M-13508C Paragraph 4.4.4	Coating Temperature (°F):


Environmental & Durability Factors	
AR: Moderate, per MIL-C-48497A Paragraph 4.5.3.3 DLC: Severe, per MIL-C-675C Paragraph 4.5.10	Coating Abrasion:
AR: per MIL-C-48497A Paragraph 4.5.3.1 DLC: per MIL-M-13508C Paragraph 4.4.6	Coating Adhesion:
AR: per MIL-C-48497A Paragraph 4.5.3.2 DLC: ≥24 Hours per MIL-C-675C paragraph 4.5.8	Coating Humidity:
AR: N/A DLC: ≥24 Hours Immersion per MIL-C-675C paragraph 4.5.7	Coating Salt Solubility:
AR: N/A ≥24 Hours per MIL-C-675C paragraph 4.5.9	Coating Salt Spray:
AR: per MIL-C-48497A Paragraph 4.5.4.2 DLC: N/A	Coating Solubility and Cleaning:
AR: N/A DLC: ≥5,000 Wipes of Sand/Slurry per TS-1888	Coating Wiper Durability:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Meets Severe Abrasion Requirements of MIL-C-675C
 - ≥90% Transmission from 8 - 11.5µm
 - Ideal for Harsh Environments
 - [Uncoated, 3-5 Micron BBAR, and 8 - 12 Micron BBAR Coated Germanium Windows](#) are also Available
 - Due to material supply chain disruptions with germanium, there may be increased lead times and price changes on our germanium products. For more information, please contact our [customer service team](#).
 - Edmund Optics has limited remaining inventory of this part number and no raw material available to supply more once this is depleted. Please contact our Product Support Engineers to help with an alternate solution for your needs. Customer Service can provide you the latest price and availability.
- TECHSPEC® Diamond-Like Carbon (DLC) Coated Germanium Windows have been designed with durability in mind. Featuring a high efficiency broadband anti-reflection coating on one surface and a specially designed [DLC coating](#) on the other surface, these windows feature excellent transmission and environmental resistance. The DLC coated surface is designed to withstand temperature cycling from -80 to +160°F, salt spray for a continuous period of 24 hours, salt solubility for an immersion period of 24 hours, and 5,000 wiper oscillations in a sand and slurry mixture. Further, TECHSPEC DLC Coated Germanium Windows meet the MIL-C-675C requirements for severe abrasion.

Technical Information



Specification	AR Coating	DLC Coating
Adhesion	per MIL-C-48497A Paragraph 4.5.3.1	per MIL-M-13508C Paragraph 4.4.6
Abrasion	Moderate, per MIL-C-48497A Paragraph 4.5.3.3	Severe, per MIL-C-675C Paragraph 4.5.10
Humidity	per MIL-C-48497A Paragraph 4.5.3.2	≥24 Hours per MIL-C-675C paragraph 4.5.8
Salt Solubility	-	≥24 Hours Immersion per MIL-C-675C paragraph 4.5.7
Salt Spray	-	≥24 Hours per MIL-C-675C paragraph 4.5.9
Temperature (°F)	-80 to +160 per MIL-C-48497A Paragraph 4.5.4.1	-80 to +160 per MIL-C-48497A Paragraph 4.5.4.1
Solubility and Cleaning	per MIL-C-48497A Paragraph 4.5.4.2	-
Water Solubility	24 Hours, per MIL-C-48497A Paragraph 4.5.5.3	-
Wiper	-	≥5,000 Wipes of Sand/Slurry per TS-1888

Special Handling

Germanium Optics Handling and Cleaning Guidelines

Germanium optics require special handling and cleaning procedures. Always wear gloves during handling to prevent contamination, and wash hands afterward. Avoid contact between Germanium dust and the eyes, skin, or clothing. When not in use, store optics sealed and covered at temperatures between 20°C and 25°C. Do not expose them to temperatures exceeding 100°C when in use.

Handling Guidelines

- Always wear [gloves](#) to prevent damage from skin oils.
- If Germanium dust is present, take the following precautions:
 - Wear safety glasses to protect eyes.
 - Use a dust mask or face mask to avoid inhalation.
 - Wear [gloves](#) to prevent skin contact.
- Maintain storage temperature between 20°C and 25°C with humidity below 30%.
- Wrap Germanium optics in a [lens cloth](#) or [pouch](#) and seal in a [container](#) when not in use.
- Germanium is brittle and heavy—always place it on soft surfaces and avoid dropping it.

Approved Cleaning Solvents

- Ethanol
- Isopropyl Alcohol
- Methanol
- Reagent-Grade Acetone
- Liquid CO₂
- [Shop Now](#)

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts
