

[See all 8 Products in Family](#)

**TECHSPEC® 50mm Diameter, 700nm Cut-On SWIR Longpass Filter**



Stock **#86-447** **7 In Stock**

MRP ₹16,546

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹16,546 each
Qty 10-25	₹14,932 each
Qty 26-49	₹14,226 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Longpass Filter **Type:**

**Physical & Mechanical Properties**

50.00 **Diameter (mm):**

1.20 ±0.15 **Thickness (mm):**

	<b>Dimensional Tolerance (mm):</b>
+0.0/-0.2	
<b>Optical Properties</b>	
	<b>Cut-On Wavelength (nm):</b>
700.00	
	<b>Substrate:</b> <input type="checkbox"/>
<b>BOROFLOAT®</b>	
	<b>Coating:</b>
Traditional Coated	
	<b>Rejection Wavelength (nm):</b>
350 - 685	
	<b>Surface Quality:</b>
80-50	
	<b>Transmission Wavelength (nm):</b>
710 - 2500	
	<b>Cut-On Wavelength (µm):</b>
0.7	
	<b>Coating Specification:</b>
T <sub>avg</sub> <0.5% @ 350 - 685nm	
T <sub>avg</sub> >85% @ 900 - 1700 nm	
T <sub>avg</sub> >70% @ 710 - 900 nm and 1700 - 2500nm	
	<b>Wavelength Range (nm):</b>
350 - 2500	
	<b>Surface Flatness (P-V):</b>
4 - 6λ	

<b>Regulatory Compliance</b>	
	<b>RoHS 2015:</b>
<b>Compliant</b>	
	<b>Certificate of Conformance:</b>
<b>View</b>	
	<b>REACH 241:</b>
<b>Compliant</b>	
	<b>Country of Origin:</b>
United States	
	<b>Imported By:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000	

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Block Visible Wavelengths
- Ideal for Machine Vision Applications
- Can Be Used as Cold Mirrors
- Additional [Longpass Edge Filters](#) Available

Designed to pass short-wave infrared (SWIR) wavelengths while blocking visible light, TECHSPEC® SWIR Longpass Filters are ideal for increasing the image quality of InGaAs cameras in a variety of machine vision applications. These longpass edge filters are offered in multiple sizes and cut-on wavelengths. TECHSPEC SWIR Longpass Filters can also be used as extended cold mirrors to eliminate damage or adverse effects caused by heat build-up.

## Technical Information



## Compatible Mounts

---