

[See all 21 Products in Family](#)

5.0mm Diameter, Ruby Half-Ball Lens



Stock #49-564 **20+ In Stock**

- 1 + MRP ₹4,011

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹4,011 each
Qty 11-49	₹3,228 each
Need More?	Request Quote

Product Downloads

General

Half-Ball Lens **Type:**

Physical & Mechanical Properties

5.00 **Diameter (mm):**

2.50 **Radius R (mm):**

Specific Gravity (g/cm³):

3.98

Thickness (mm):

2.50

Compressive Strength (psi):

300,000

Diameter Tolerance (μm):

± 2.54

Optical Properties

Substrate:

Ruby Doped Sapphire (Al_2O_3)

Coating:

Uncoated

Index of Refraction (n_d):

1.77

Sphericity (μm):

0.64

Environmental & Durability Factors

Melting Temperature ($^{\circ}\text{C}$):

2053.00

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

Country of Origin:

Switzerland

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Excellent for Severe Environments
- High Chemical Stability
- [Sapphire and Ruby Ball Lenses](#) Also Available

Sapphire and Ruby Half-Ball Lenses feature a very short back focal length with the convenience of a flat surface for easy mounting. Sapphire features a high index of refraction and excellent broadband transmission characteristics. Ruby half-ball (hemispherical) lenses are easier to see and, therefore, easier to handle for physical applications. Sapphire and Ruby Half-Ball Lenses are very chemically stable and are great for severe environments, high-temperature applications, and applications requiring high melting points. Typical applications include fiber communication, endoscopy, microscopy, optical pick-up devices, and laser measurement systems.

Technical Information



