

## 50mm Diameter, X-Y-Z Positioning Movement



50mm Diameter, X-Y-Z Positioning Movement, #03-607

Stock **#03-607** **20+ In Stock**

⊖ 1 ⊕ MRP ₹98,368

📌 Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹98,368 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Metric **Type:**

**Note:**  
50mm Inner Diameter Optical Mount Included for VZMLens Mounting

### Physical & Mechanical Properties

Linear (X-Y-Z) **Type of Movement:**

**Guide System:**

Dovetail

76.2 x 90 **Stage Size (mm):**

70 in X, 60 in Y, 65 in Z **Travel (mm):**

2.75 in X, 2.36 in Y, 2.56 in Z **Travel (inches):**

18 in X, 18 in Y, 23 in Z **Travel Per Knob Rotation (mm):**

1.2 **Weight (kg):**

## Hardware & Interface Connectivity

Rack and Pinion **Type of Drive:**

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **REACH 241:**

Japan **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

### 1/4-20 Adapter Plate Accessory

This item is used in conjunction with the X-Y-Z Positioning Movement (#03-607). This adapter plate accessory permits the positioning of mounting components to the stage and replaces the existing mounting ring attached to #03-607, which includes two M3 socket head cap screws to allow for mounting 1/4-20 Plate Accessory #54-491.

- 50mm Diameter Optical Mount
- Includes Durable Mounting Base
- Helical Rack and Pinion Drive Mechanism

The X-Y-Z Positioning Movement allows for exact positioning in the vertical, horizontal, and depth planes. The precise helical rack and pinion design gives this component the accuracy, durability, and travel required for optical system integration. The mechanism's 50mm inner dia. x 23.5mm thick mounting ring is ideal for holding cylindrical lasers, mounted corner cubes, etc. The X-Y-Z Positioning Movement ring mount assembles quickly with a Phillips screwdriver (not included). The optional 1/4-20 adapter plate accessory allows additional component mounting. This mechanism weighs 2.7 lbs.

### 1/4-20 Adapter Plate Accessory (#54-491)

This item is used in conjunction with the X-Y-Z Positioning Movement (#03-607). This adapter plate accessory permits the positioning of mounting components to the stage and replaces the existing mounting ring attached to #03-607, which includes two M3 socket head cap screws to allow for mounting 1/4-20 Plate Accessory #54-491.

## Technical Information

