

TECHSPEC[®] 50mm Travel, 80mm Square TECHSPEC Motorized Linear Stage, Metric



50mm Travel, 80mm Square TECHSPEC Motorized Linear Stage, Metric

Stock **#72-700** **1 In Stock**

-

1

+

₹1,98,000

ADD TO CART

Volume Pricing	
Qty 1+	₹1,98,000 each
Need More?	Request Quote

Product Downloads

General	
Metric	Type:
Stepper Motor	Type of Motor:
Physical & Mechanical Properties	
Linear (X)	Type of Movement:
Ball Bearing	Guide System:

80 x80	Stage Size (mm):
50	Travel (mm):
5	Accuracy (µm):
<1	Backlash (µm):
Stainless Steel	Construction:
30	Height (mm):
8	Load Capacity (kg):
20	Parallelism (µm):
±0.5	Repeatability (µm):
20	Speed (mm/s):
1.35	Weight (kg):
16,000 PPR	Encoder Resolution:

Optical Properties

5	Resolution (µm):
---	------------------

Hardware & Interface Connectivity

Lead Screw	Type of Drive:
RS-485, USB	Control Interface:
RS-485, USB	Computer Interface:

Threading & Mounting

(9) M6 x 1.0, (4) M3 x 0.5, (8) M2 x 0.4	Mounting Threads:
--	-------------------

Environmental & Durability Factors

0-50	Operating Temperature (°C):
------	-----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
Taiwan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- High Precision, Monobloc Designs
- Integrated Motor and Controller
- Compatible with TECHSPEC Manual Stages

TECHSPEC Stainless Steel Motorized Linear Stages are a high-precision motion control solution for automated system alignment. The monobloc stainless steel design features ball bearing guides cut directly into the stage chassis, ensuring higher stiffness, straightness, and parallelism than typical stage assemblies. These motorized stages utilize the same mounting hole patterns as [TECHSPEC Manual Stages and Slides](#), allowing for the creation of combined manual and motorized optical systems, depending on the application's needs; this versatility is unique to Edmund Optics. TECHSPEC Stainless Steel Motorized Linear Stages are easily programmable and daisy chain compatible, ensuring fast setup of multi-axis automated systems. The stages deliver high precision for demanding photonics applications.