

[See all 5 Products in Family](#)

50X Mitutoyo WLI Plan Apo Objective

See More by [Mitutoyo](#)



50X Mitutoyo WLI Plan Apo Objective

Stock #74-660 **NEW** 1 In Stock

1 ₹9,61,350

ADD TO CART

Volume Pricing	
Qty 1+	₹9,61,350 each
Need More?	Request Quote

Product Downloads

General

378-403 **Model Number:**

Compatible Tube Lens Focal Length (mm):
Focal Length: 100mm

Infinity Corrected **Style:**

Mitutoyo **Manufacturer:**

Note:

Designed to be used with a 100mm Tube Lens, Sold Separately

Physical & Mechanical Properties

58.00 **Length (mm):**

40.00 **Maximum Diameter (mm):**

300.00 **Weight (g):**

Optical Properties

0.18mm **Horizontal Field of View, 2/3" Sensor:**

2.00 **Focal Length FL (mm):**

50X **Magnification:**

0.70 **Numerical Aperture NA:**

0.39 **Resolving Power (μm):**

0.56 **Depth of Field (μm):**

2.00 **Working Distance (mm):**

11.00 **Field Number (mm):**

60.00 **Parfocal Length (mm):**

Sensor

2/3" **Maximum Sensor Format:**

Threading & Mounting

RMS/20.32mm x36 TPI **Mounting Threads:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Japan **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

Product Details

- Ideal for Interferometry Applications
- Long Working Distances and High Numerical Apertures
- High-Quality Plan Apochromatic Design

Mitutoyo WLI Plan APO Infinity Corrected Objectives are high-resolution plan apochromatic objectives featuring high numerical apertures designed for use in white light interferometry applications. These objectives ensure long parfocal working distances of 60mm while maintaining a more compact and lightweight design. Each objective incorporates an interference fringe adjustment mechanism and internal beam splitter for precise measurements and control of the interference fringe pattern. Mitutoyo WLI Plan APO Infinity Corrected Objectives are available with magnifications ranging from 2.5 – 50x and are designed for use with 100mm focal length tube lenses. These objectives are ideal for white light interferometry applications such as Vertical Scanning Interferometry (VSI), 3D Surface Profiling, Dispersion & Reflection Measurement, and Medical Imaging.