

[See all 6 Products in Family](#)

TECHSPEC® 515, 1030nm, 25.4mm Dia., Dual Band Low GDD Mirror



Stock #17-287 **20+ In Stock**

MRP ₹36,825

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹36,825 each
Qty 6-9	₹32,487 each
Qty 10+	₹28,956 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror **Type:**

Typical Applications:
Beam transport of 1st and 2nd harmonic of Yb:doped lasers

Physical & Mechanical Properties

Parallelism (arcmin):

<3

Clear Aperture (%):

>86

Back Surface:

Commercial Polish

Diameter (mm):

25.40 +0/-0.1

Thickness (mm):

6.35 ±0.20

Optical Properties

Surface Quality:

10-5

Coating Specification:

$R_s > 99.9\%$ @500-540nm
 $R_p > 99.8\%$ @507-527nm
 $R_s > 99.9\%$ @1000-1070nm
 $R_p > 99.8\%$ @1005-1070nm

GDD Specification:

$< 35\text{fs}^2$ @ 500 - 540nm (s-pol)
 $< 50\text{fs}^2$ @ 510 - 525nm (p-pol)
 $< 20\text{fs}^2$ @ 1000 - 1070nm (s-pol)
 $< 40\text{fs}^2$ @ 1010 - 1055nm (p-pol)

Wavelength Range (nm):

500 - 540, 1000 - 1070

Surface Flatness (P-V):

$< \lambda/6$ @632.8nm over 20mm aperture

Coating Type:

S1: Dielectric
S2: Stress-compensating

Coating:

Ultrafast (500-540, 1000-1070nm)

Design Wavelength DWL (nm):

515, 1030

Angle of Incidence (°):

45

Substrate:

[Fused Silica](#) (Corning 7980)

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Germany

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- High Reflectivity & Low Group Delay Dispersion (GDD) for Ultrafast Beam Steering
- Ion-Beam Sputtered (IBS) Coatings Minimize Scatter and Absorption Losses
- Near-Zero GDD for Both the First and Second Harmonics of Ti:sapphire and Yb-doped Lasers

TECHSPEC® Dual Band Low GDD Ultrafast Mirrors maintain high reflectivity and near-zero group delay dispersion over both the first and second harmonic of Ti:sapphire and Yb-doped lasers. Utilizing Ion-Beam Sputtered Coating Technology, these mirrors minimize scatter and absorption loss commonly observed when using other traditional coating application processes. TECHSPEC® Dual Band Low GDD Ultrafast Mirrors are often used in beam steering applications as they will maintain ultrashort pulse durations that can be difficult to preserve when using more conventional laser mirrors. These mirrors are ideal for second-harmonic generation (SHG) microscopy and spectroscopy applications as well as for frequency resolved optical gating (FROG).

Compatible Mounts