

[See all 30 Products in Family](#)

TECHSPEC® 515nm, 12.7mm Dia. x 6.35mm Thickness, Ultrafast Laser Mirror



Stock #25-092 **20+ In Stock**

⊖ 1 ⊕ ₹7,396

ADD TO CART

Volume Pricing	
Qty 1-5	₹7,396 each
Qty 6+	₹6,617 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

6.35 ±0.20 **Thickness (mm):**

12.70 +0.0/-0.1 **Diameter (mm):**

90 **Clear Aperture (%):**

Commercial Polish	Back Surface:
<3	Parallelism (arcmin):
Optical Properties	
Fused Silica (Corning 7980)	Substrate: <input type="checkbox"/>
10-5	Surface Quality:
45	Angle of Incidence (°):
Ultrafast (500-530nm)	Coating:
515	Design Wavelength DWL (nm):
480 - 530	Wavelength Range (nm):
λ/8	Surface Flatness (P-V):
Coating Specification: R _(avg) S & P >99.90% @ 515nm @ 45° AOI R _(avg) >99.7% @ 500 - 530nm @ 45° AOI	
Dielectric	Coating Type:
GDD Specification: ±10 fs ² @ 480 - 540nm @ 45° AOI (s-pol) ±20 fs ² @ 500 - 530nm @ 45° AOI (p-pol)	
Damage Threshold, Pulsed: 0.2 J/cm ² , 150fs @ 515nm	

Environmental & Durability Factors

ML-PRF-13830B	Durability:
---------------	--------------------

Regulatory Compliance

View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- GDD as Low as ±20fs² at Design Wavelength Range
- Greater than 99.9% Reflectivity
- Ideal for Ti:sapphire and Yb:doped Ultrafast Lasers

TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors feature a multilayer dielectric coating on fused silica substrates for excellent reflectivity of greater than 99.9%, and low coefficient of thermal expansion, making them ideal for ultrafast beam transport applications. These mirrors have a group delay dispersion (GDD) of near zero at their design wavelength range, minimizing dispersion of the reflected beam. TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors are ideal for utilizing the first and second harmonic of Ti:sapphire and Yb:doped lasers for applications such as laser machining and welding.

Note: Please [contact us](#) if your application requires a TECHSPEC Low GDD Ultrafast Mirror with a custom wavelength, angle, or size.