

37mm Max. Aperture, Iris Diaphragm



Stock #32-618 **10 In Stock**

- 1 + MRP ₹9,534

i Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-4 | ₹9,534 each |
| Qty 5-9 | ₹8,444 each |
| Qty 10+ | ₹7,829 each |
| Need More? | Request Quote |

Product Downloads

General

Unmounted **Type:**

Physical & Mechanical Properties

37.0 **Maximum Aperture (mm):**

53.0 **Outer Diameter (mm):**

| | |
|---|-------|
| Construction: | |
| Brass Housing, Blue Tempered Steel Leaves | |
| Lever Diameter (mm): | 3.00 |
| Lever Length (mm): | 12.50 |
| Number of Leaves: | 16.00 |
| Thickness (mm): | 6.00 |

Optical Properties

| | |
|-------------------------------|-----|
| Minimum Aperture (mm): | 1.9 |
|-------------------------------|-----|

Regulatory Compliance

| | |
|------------------------------------|---|
| RoHS 2015: | Exempt |
| Certificate of Conformance: | View |
| Reach 247: | Contains SVHC(s) |
| Country of Origin: | Germany |
| Imported By: | Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000 |

Product Details

- Used to Adjust f#, Field Stop Diameter, and Overall Light Throughput
- Mounted Version Features a Tapped Hole for Post Mounting
- Abundant Types for Varying Applications


Standard Series Iris Diaphragms can provide control of system f# (f# = focal length/effective diameter), field stop diameter, and overall energy throughput when incorporated into standard optical systems. It should be noted that the location of the iris is critical to how it will affect the system. All of these diaphragms offer exceptionally smooth operation over the lever travel, from maximum to minimum aperture (approximately 90°). Mounted versions of these diaphragms feature a tapped hole for easy post mounting. Standard Series Iris Diaphragms have blued spring steel leave construction and black housing finish with lever actuators that are available in two styles: stainless steel "pin" or plastic "tab." These diaphragms are specifically designed for OEM integration and general laboratory use.

For specific OEM application assistance, please contact our [Applications Engineering Department](#).

Note: Iris Diaphragm Mounts sold separately.

Technical Information

Types of Levers



| Outside Diameter A | Maximum Aperture B | Minimum Aperture C | Thickness D | Stock No. |
|--------------------|--------------------|--------------------|-------------|-------------------------|
| 10.0 | 5.0 | 0.60 | 4.50 | #54-352 |
| 14.8 | 8.00 | 0.80 | 4.50 | #32-623 |
| 15.5 | 8.50 | 1.00 | 5.30 | #42-124 |
| 19.8 | 12.0 | 0.80 | 5.0 | #30-263 |
| 22.0 | 14.0 | 1.0 | 6.0 | #42-123 |
| 24.0 | 15.0 | 1.2 | 5.0 | #32-622 |
| 28.0 | 18.0 | 1.2 | 5.0 | #32-621 |
| 30.0 | 20.0 | 1.2 | 5.5 | #35-111 |
| 31.0 | 18.0 | 1.5 | 6.5 | #36-623 |

| | | | | |
|-------|-------|------|------|---------|
| 33.0 | 22.0 | 1.4 | 5.5 | #32-620 |
| 37.0 | 25.0 | 0.8 | 5.5 | #35-110 |
| 40.0 | 28.0 | 1.5 | 5.5 | #42-122 |
| 42.0 | 42.6 | 1.2 | 5.8 | #40-997 |
| 42.0 | 30.0 | 1.5 | 6.0 | #64-500 |
| 48.0 | 48.0 | 1.2 | 6.8 | #40-998 |
| 48.5 | 30.0 | 1.2 | 7.0 | #42-121 |
| 49.0 | 34.0 | 1.5 | 6.5 | #41-972 |
| 50.0 | 36.0 | 1.9 | 6.0 | #32-619 |
| 53.0 | 37.0 | 1.9 | 6.0 | #32-618 |
| 55.0 | 41.0 | 2.0 | 6.5 | #41-973 |
| 58.0 | 42.0 | 2.0 | 6.5 | #30-118 |
| 60.0 | 40.0 | 2.5 | 7.8 | #36-624 |
| 70.0 | 50.0 | 2.5 | 7.5 | #32-617 |
| 77.0 | 59.0 | 7.0 | 8.0 | #32-616 |
| 80.0 | 58.0 | 3.0 | 8.0 | #32-615 |
| 82.0 | 60.0 | 4.0 | 10.1 | #36-625 |
| 92.0 | 70.0 | 4.5 | 9.0 | #32-614 |
| 100.0 | 75.0 | 4.5 | 9.0 | #30-264 |
| 110.0 | 80.5 | 4.5 | 10.0 | #32-613 |
| 120.0 | 90.0 | 5.0 | 12.0 | #32-612 |
| 130.0 | 98.0 | 5.0 | 12.0 | #32-611 |
| 140.0 | 104.0 | 5.0 | 11.0 | #32-610 |
| 150.0 | 110.0 | 6.0 | 13.0 | #60-644 |
| 165.0 | 120.0 | 6.0 | 15.0 | #32-609 |
| 180.0 | 138.0 | 11.5 | 13.0 | #32-608 |
| 208.0 | 158.0 | 11.0 | 16.0 | #70-894 |
| 300.0 | 225.0 | 12.0 | 19.0 | #70-895 |

