

[See all 36 Products in Family](#)

550nm, 25mm Dia., OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock **#15-225** **20+ In Stock**

MRP ₹11,603

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹11,603 each
Qty 10-25	₹10,493 each
Qty 26-49	₹9,787 each
Need More?	Request Quote

Product Downloads

General

Longpass Filter **Type:**

Physical & Mechanical Properties

25.00 +0.00/-0.20 **Diameter (mm):**

Thickness (mm):

2.00 ±0.10

90 **Clear Aperture (%):**

Physical Durability:
ML-C-48497A, Section 3.4.1

Optical Properties

0 **Angle of Incidence (°):**

≥2.0 **Optical Density OD (Average):**

550.00 ±11 **Cut-On Wavelength (nm):**

Substrate:
BOROFLOAT®

Hard Coated **Coating:**

400 - 525 **Rejection Wavelength (nm):**

60-40 **Surface Quality:**

≥85 **Transmission (%):**

575 - 1600 **Transmission Wavelength (nm):**

400 - 1600 **Wavelength Range (nm):**

Environmental & Durability Factors

Environmental Durability:
ML-STD-810F, Section 507.4

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 250:
Compliant

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Sharp Cut-On Wavelength
- ≥85% Transmission and OD 2.0 Blocking
- 6mm Square or 12.5/25mm Diameter Sizes
- [TECHSPEC® OD 4.0 Longpass Filters](#) Also Available

OD 2.0 Longpass Filters are cost-effective filters with cut-on wavelengths ranging from 400 to 950nm. These longpass filters provide ≥85% transmission across a transmission band that extends out to 1600nm while providing OD 2.0 blocking across their rejection band. The back surface of each filter is coated with an antireflection (AR) coating, increasing the overall efficiency of the filter. OD 2.0 Longpass Filters can be combined with OD 2.0 Shortpass Filters to create custom bandpass filters to meet application requirements in the visible or near-infrared. These longpass filters are ideal for use in fluorescence applications or separating spectral orders, with the 6 x 6mm sized filters suitable for integration into optical instrumentation requiring cost-effective, lightweight filters.

Technical Information

OD 2.0 Longpass Filters



Compatible Mounts

;