

TECHSPEC® 5mm Aperture, 30mm L, VIS-EXT Coated, High NA, Hexagonal Light Pipe



N-BK7 Light Pipe Homogenizing Rods



Stock #72-731 **5 In Stock**

⊖ 1 ⊕ MRP ₹16,249

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹16,249 each
Qty 6-25	₹13,063 each
Qty 26-49	₹12,213 each
Need More?	Request Quote

Product Downloads

General

Light Pipe **Type:**

Physical & Mechanical Properties

Length (mm):

30.00	Parallelism (arcmin):
<5.00	
<hr/>	
	Length Tolerance (mm):
±0.20	
<hr/>	
	Light Source NA:
High	

Optical Properties

MS-EXT (350-700nm)	Coating:
N-BK7	Substrate: □
<hr/>	
60-40	Surface Quality:
5.00	Entrance and Exit Aperture (mm):
<hr/>	
±0.10	Aperture Tolerance (mm):
Light Homogenization	Image Orientation:
<hr/>	
$R_{avg} \geq 0.5\% @ 350 - 700nm$	Coating Specification:
350 - 700	Wavelength Range (nm):
<hr/>	
1λ	Surface Flatness (P-V):

Regulatory Compliance

View	Certificate of Conformance:
<hr/>	
China	Country of Origin:
<hr/>	
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Homogenizes Non-Uniform Light Sources
- Hexagonal Entrance Aperture
- Uncoated and MS-EXT Coated Options Available
- Ideal for OEM Illumination
- Additional [Light Pipe Homogenizing Rods](#) Available

TECHSPEC® N-BK7 Light Pipe Homogenizing Rods utilize total internal reflection to homogenize non-uniform light sources regardless of spectral characteristics. Their hexagonal configurations provide 35% less light loss than a comparable square configuration. Low Numerical Aperture (NA) sources require longer pipes to uniformly homogenize light, while shorter pipes will sufficiently homogenize the output from high NA sources. TECHSPEC N-BK7 Light Pipe Homogenizing Rods are made from precision N-BK7 for use in a variety of visible light applications and are available uncoated or with MS-EXT coatings.

[Fused silica versions](#) of our light pipe homogenizing rods are also available. [TECHSPEC® Light Pipe Homogenizing Rod Mounts](#), specifically designed to hold our standard and fused silica families of light pipe homogenizing rods, are available; these mounts greatly simplify the handling and integration of these components.

Technical Information



