

**TECHSPEC® 5mm Dia Enhanced Aluminum, 4-6λ Mirror**



Stock #32-940 **20+ In Stock**

- 1 + MRP ₹2,876

**i** Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹2,876 each                   |
| Qty 6-25       | ₹2,220 each                   |
| Qty 26-99      | ₹2,018 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Flat Mirror **Type:**

**Physical & Mechanical Properties**

5.00 ±0.25 **Diameter (mm):**

2.00 nominal **Thickness (mm):**

|   |  |
|---|--|
| 4.00                                      | <b>Clear Aperture CA (mm):</b>                               |
| ±0.25                                     | <b>Dimensional Tolerance (mm):</b>                           |
| Ground, 0.5mm Maximum Edge Chip           | <b>Edges:</b>  |
| <b>Optical Properties</b>                 |  |
| Metal                                     | <b>Coating Type:</b>   |
| Enhanced Aluminum (450-650nm)             | <b>Coating:</b>  |
| 4 - 6λ                                    | <b>Surface Flatness (P-V):</b>                               |
| 450 - 650                                 | <b>Wavelength Range (nm):</b>                                |
| Float Glass                               | <b>Substrate:</b> <input type="checkbox"/>                   |
| R <sub>avg</sub> ≥95% @ 450 - 650nm @ 45° | <b>Coating Specification:</b>                                |
| 60-40                                     | <b>Surface Quality:</b>                                      |
| 0.2 J/cm <sup>2</sup> @ 532nm, 10ns       | <b>Damage Threshold, By Design:</b> <input type="checkbox"/> |

|   |                                    |
|---|------------------------------------|
| <b>Regulatory Compliance</b>  |                                    |
| Compliant   | <b>RoHS 2015:</b>                  |
| View  | <b>Certificate of Conformance:</b> |
| Compliant   | <b>Reach 247:</b>                  |
| United States   | <b>Country of Origin:</b>          |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 | <b>Imported By:</b>                |


## Product Details

- Wide Variety of Shapes and Sizes Available
- Enhanced Aluminum, Protected Gold, and Protected Silver Coatings for high reflectivity from 450-10000nm
- [Contact Us](#) for Custom Sizes

TECHSPEC® First Surface Mirrors feature a high reflectivity coating deposited on the front surface of the glass substrate. The mirrors are available in enhanced aluminum, protected gold, and protected silver coatings for high reflectivity from 450-10000nm. The coated surface should be oriented to reflect incident light. TECHSPEC First Surface Mirrors are offered in circular, square, and rectangular dimensions. First surface mirrors are ideal for applications requiring the mirror to be mounted at 45° in order to produce a 90° bend in the light path. These first surface mirrors easily mount into a [range of optical mounts](#) to facilitate application integration.

Note: A range of mounts specifically compatible with individual TECHSPEC® First Surface Mirrors can be found on product web pages.

## Technical Information



## Coating Curves

## Compatible Mounts

