

[See all 36 Products in Family](#)

TECHSPEC® 5mm Dia. x 4mm FL, MgF₂ Coated, Molded Aspheric Condenser Lens



TECHSPEC Molded Aspheric Condenser Lenses

Stock **#15-189** [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕ MRP ₹3,581

Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | ₹3,581 each |
| Qty 11-49 | ₹3,228 each |
| Need More? | Request Quote |

Product Downloads

General

Condenser Lens **Type:**

Note:
[Click here](#) for more information on the ISO 10110 surface quality specification.

Physical & Mechanical Properties

Diameter (mm):

| | |
|----------------------|----------------------------------|
| 5.00 +0.0/-0.2 | Centering (arcmin): |
| ≤25 | |
| 4.35 | Clear Aperture CA (mm): |
| 2.14 | Edge Thickness ET (mm): |
| 3.88 ±0.30 | Center Thickness CT (mm): |
| Protective as needed | Bevel: |
| 5.00 | Diameter of Asphere (mm): |
| Plano | Shape of Back Surface: |

Optical Properties

| | |
|---|--|
| 4.00 @ 587.6nm | Effective Focal Length EFL (mm): |
| 0.62 | Numerical Aperture NA: |
| 1.45 | Back Focal Length BFL (mm): |
| Liba2000+ | Substrate: <input type="checkbox"/> |
| ±5 | Focal Length Tolerance (%): |
| MgF ₂ (400-700nm) | Coating: |
| R _{avg} ≤1.75% @400 - 700nm | Coating Specification: |
| Molded Side: 5/3 x 0.4; E 0.2 Polished Side: 5/3 x 0.25; E 0.2 | Surface Quality: |
| 0.8 | f#: |
| 58.9 | Abbe Number (v_d): |
| 587.6 | Design Wavelength DWL (nm): |
| 1.52 | Index of Refraction (n_d): |
| ∞ | Radius R₂ (mm): |
| 400 - 700 | Wavelength Range (nm): |
| Infinite | Conjugate Distance: |
| 587.6 | Focal Length Specification Wavelength (nm): |

Material Properties

| | |
|-----|---|
| 9.4 | Coefficient of Thermal Expansion CTE (10⁻⁶/°C): |
|-----|---|

Regulatory Compliance

| | |
|---|------------------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 235: |
| Germany | Country of Origin: |
| Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000 | Imported By: |

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements.

Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- High Numerical Apertures
- Fully Documented for OEM Integration
- Ideal for Illumination Applications

TECHSPEC® Molded Aspheric Condenser Lenses have been designed for integration into the illumination path of OEM instrumentation. Available in 5 to 50mm diameters, the small diameter lenses are ideal for medical devices or portable instruments, while the larger lenses are typically integrated into benchtop analytical equipment including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms. The front aspheric surface is molded to eliminate spherical aberrations, while the second surface is ground and polished for improved performance. Full prescription data and drawings are available to aid in design integration.

Note: For custom coating options, please [contact us](#).

Coating Curves

Compatible Mounts