

[See all 16 Products in Family](#)

600mm Cobra Max Red Line Light



600mm Cobra MaxLine Light



Stock **#73-957** [CONTACT US](#)

1 MRP ₹10,45,008

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹10,45,008 each
Need More?	Request Quote

Product Downloads

General

Type of Illumination:
LED

Note:
Lights are fan cooled. See datasheet for additional mounting, spectral, and irradiance information

Manufacturer:
ProPhotonix

Line Light	Geometry:
Ethernet Controlled, Continuous	Illumination Mode:
Physical & Mechanical Properties	
600.00	Length (mm):
600.00 x 173.50	Dimensions (mm):
Collimated (M2)	Lens Position:
Optical Properties	
Red	Color:
20.00	Full Width-Half Max FWHM (nm):
630	Wavelength:
20-300	Working Distance (mm):
Hardware & Interface Connectivity	
Straight	Connector:
24	Operating Voltage (V):
Power Supply: Power supply required and sold separately. USA: #73-977	
Length of Cable (m): 2m braided power cable included	
Threading & Mounting	
Aluminum T-Slot Extrusion	Mount:
Regulatory Compliance	
View	Certificate of Conformance:
Ireland	Country of Origin:
Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Product Details

- Intensities up to 3140kLux
- 100, 300, or 600mm Length Options Available
- White, Red, Multispectral, and SWIR Illumination Options Available

ProPhotonix COBRA™ MAX LED Line Lights are slim, compact LED line lights available in lengths of 100, 300, or 600mm in red, white, multispectral, or SWIR illumination options. These line lights feature Chip-on-Board LED technology which offers greater uniformity, thermal performance, and intensity while maintaining a compact size compared to traditional surface mount LED constructions. ProPhotonix COBRA™ MAX LED Line Lights multispectral option offers RGB-IR illumination and the ability to control each wavelength independently. The available easy-to-use comprehensive software package can be customized to meet specific application needs and is downloadable from a QR code included with the units. These lights are ideal for many linescan inspection applications such as solar cell inspection, semiconductor inspection, food sorting, and flat panel display inspection.

Note: Required 24V Power Supply, [#73-977](#), sold separately. Optional Lens Kits are available to adjust the working distance by changing the position of the projection lens.