

[See all 13 Products in Family](#)

60mm Center of Rotation, High Vacuum (10^{-6} Torr) Motorized Goniometer Stage, Integrated Controller

See More by [Zaber™](#)



Stock #74-721 **NEW** 1 In Stock

MRP ₹6,44,687

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹6,44,687 each
Need More?	Request Quote

Product Downloads

General

Metric **Type:**

No **Encoder:**

No **Manual Control/ LED Indicators:**

Manufacturer:

X-GSM60-SV2T9 **Model Number:**

Requires Accessory Kit, [#75-301](#), for operation. **Note:**

2-Phase Stepper **Type of Motor:**

Physical & Mechanical Properties

Goniometer **Type of Movement:**

Crossed Roller Bearing **Guide System:**

72.7 x 116.3 **Stage Size (mm):**

±7 **Travel (°):**

0.06 **Accuracy (°):**

<0.01 **Backlash (°):**

20.8 **Height (mm):**

3 **Load Capacity (kg):**

30 **Load Capacity (N):**

60 **Radius R (mm):**

<0.005 **Repeatability (°):**

<0.087 **Resolution (µrad):**

0.000069 - 30 **Speed (°/s):**

0.32 **Weight (kg):**

Electrical

350 **Current (mA):**

350 **Maximum Operating Current (mA):**

Hardware & Interface Connectivity

Precision Worm Gear **Type of Drive:**

24-48 VDC; Power Supply w/US Plug found in accessories kit, [#75-301](#) **Power Supply:**

RS-232, USB **Computer Interface:**

Material Properties

High vacuum (10^{-6} Torr) **Vacuum Compatibility:**

Environmental & Durability Factors

0 to +50 **Operating Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

Canada **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Product Details

- Low Vacuum (10^{-3} Torr) and High Vacuum (10^{-6} Torr) Options Available
- 360° Rotational, Linear, or Vertical Travel Stages, and Goniometer Options Available
- Controlled via Minimal Feed-Through Wires

Zaber™ Vacuum Compatible Motorized Stages are designed for integration into vacuum systems and are available in high vacuum 10^{-6} Torr stages or low vacuum 10^{-3} Torr configurations (upon request). The stage body components are specifically engineered to limit outgassing of contaminants in the vacuum chamber, the included stepper motors are designed for thermal management in high vacuum environments, and the stages can be connected to a computer interface with minimal feed-through wires. Zaber™ Vacuum Compatible Motorized Stages are available in linear, 360° rotational, and goniometric configurations, allowing for a complete 6 Degree-of-Freedom system to be constructed in a vacuum. These stages are ideal for applications operating in high vacuum conditions, such as semiconductor manufacturing and processing, or optical coating processes.

Note: An accessories kit, [#75-301](#), is required and sold separately.
