

## 632.8nm, $\lambda/4$ Precision Zero Order Retarder



Stock #49-220 **2 In Stock**

1  MRP ₹76,173

**Price inclusive of all taxes**

**ADD TO CART**

### Volume Pricing

Qty 1-5	₹76,173 each
Qty 6+	₹60,534 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Polymer Waveplate **Type:**

### Physical & Mechanical Properties

10.16 **Clear Aperture CA (mm):**

**Diameter (mm):**

25.40	
±0.508	<b>Thickness Tolerance (mm):</b>
±0.127	<b>Dimensional Tolerance (mm):</b>
Birefringent Polymer Stack	<b>Construction:</b>
<b>Optical Properties</b>	
632.8	<b>Design Wavelength DWL (nm):</b>
Polymer Film on <a href="#">N-BK7</a>	<b>Substrate:</b> <input type="checkbox"/>
0.5	<b>Reflection (%):</b>
$\lambda/4$	<b>Retardance:</b>
40-20	<b>Surface Quality:</b>
$\leq \lambda/5$ @ 632.8nm	<b>Transmitted Wavefront, RMS:</b>
$\lambda/350$	<b>Retardance Tolerance:</b>
1.00	<b>Beam Deviation (arcmin):</b>
500 W/cm <sup>2</sup>	<b>Damage Threshold, By Design:</b> <input type="checkbox"/>
0	<b>Retardance Order:</b>

### Threading & Mounting

6.35	<b>Mount Thickness (mm):</b>
------	------------------------------

### Environmental & Durability Factors

-20 to +50	<b>Operating Temperature (°C):</b>
------------	------------------------------------

### Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>REACH 241:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- $\lambda/4$  and  $\lambda/2$  Retardance
- Excellent Angular Field of View
- Birefringent Polymer Stack
- High Damage Threshold of 500 W/cm<sup>2</sup>

Precision Zero Order Waveplates (Retarders) feature carefully aligned birefringent polymer sheets laminated between two precision N-BK7 windows, and are available in standard  $\lambda/4$  and  $\lambda/2$  options for common visible and NIR wavelengths. These polymer waveplates (retarders) offer excellent angular field of view because they are true zero-order retarders. Also, they will experience less than 1% retardance change over a  $\pm 10^\circ$  angle of incidence. Each Precision Zero Order Waveplates (Retarders) is mounted in a metal ring with the fast axis clearly marked.