

632nm Radial Polarization Converter



Stock **#89-447** [CONTACT US](#)

-

1

+

₹3,43,319

ADD TO CART

Volume Pricing	
Qty 1+	₹3,43,319 each
Need More?	Request Quote

Product Downloads

General

Type:

Polarization Converter

Physical & Mechanical Properties

Clear Aperture CA (mm):

6.0

Diameter (mm):

25.40

Thickness (mm):

3.00 ±0.1

Dimensional Tolerance (mm):

+0.0/-0.1	
Self-Organized Nanogratings	Construction:
Optical Properties	
632	Design Wavelength DWL (nm):
Fused Silica (Corning 7980)	Substrate: ☐
20-10	Surface Quality:
80-94 (wavelength dependent)	Transmission (%):
612 - 652	Wavelength Range (nm):
λ/8	Surface Flatness (P-V):
20 J/cm ² @ 1064nm, 3.5ns	Damage Threshold, By Design: ☐
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
Lithuania	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Converts Linear Polarization to Radial or Azimuthal
- Converts Circular Polarization to an Optical Vortex (Donut-Shaped Beam)
- High Damage Thresholds in the Nano- and Femtosecond Range
- Higher-Order Versions Can Generate Higher Order Polarization Patterns and Optical Vortices

Radial Polarization Converters (S-waveplates) are space-variant retarders designed to convert linear polarization to radial or azimuthal polarization to reduce laser beam spot size. Alternatively, they can be used to convert circularly polarized light to an optical vortex (donut-shaped beam). The converters are manufactured by inscribing self-organized nanogratings inside fused silica using a femtosecond laser. Radial Polarization Converters (S-waveplates) are beneficial for a variety of polarization-sensitive applications. Radially polarized beams are highly efficient at micro-drilling high aspect-ratio features in metal, while vortex (donut-shaped) beams are ideal for STED or two-photon excitation fluorescence microscopy, laser micromachining, and optical tweezer applications (multiple particle trapping).

Higher Order Radial Polarization Converters (S-Waveplates) can generate higher order polarization patterns, optical vortices with increased topological charge, or vector Bessel beams when used in combination with [axicons](#). These types of beams are used in micromachining applications, such as microhole drilling of transparent materials.

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

Technical Information

