

[See all 6 Products in Family](#)

TECHSPEC® 6.35mm Optic Dia., E-Series Compact Kinematic Mount



6.35mm Optic Dia., E-Series Compact Kinematic Mount



Stock #72-570 **NEW** 20+ In Stock

- 1 + MRP ₹5,098

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹5,098 each
Need More?	Request Quote

Product Downloads

General

Adjustable - Tip-Tilt **Type:**

Circular **Type of Optics:**

2 **Number of Adjustment Screws:**

Plate Dimensions (mm):

Physical & Mechanical Properties

5.35 **Clear Aperture CA (mm):**

19.60 **Thickness (mm):**

No Z-Axis Translation **Travel (mm):**

Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings **Construction:**

±5.0 **Fine Tilt Angle (°):**

±5.0 **Fine Tip Angle (°):**

0.25 **Adjustment Screw Pitch (mm):**

1.90 **Min. Thickness of Compatible Optics (mm):**

12.7 **Centerline Height (mm):**

Threading & Mounting

6.35 **Size of Compatible Optics (mm):**

M4 x 0.7 **Compatible Post:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

Taiwan **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Product Details

- M3 x 0.2 Fine Adjustment Screw Threads
- <25mm Overall Profile
- Lockable for Improved Stability

Our TECHSPEC® Compact Kinematics are designed to retain the performance of a larger kinematic for integration into space sensitive applications. These kinematics feature completely reseding adjustment screws for integration into OEM applications. TECHSPEC Compact Kinematic Mounts have two front plate models for utilization of set screw or adhesive optic securing. Stainless steel inserts are also used to ensure quality and stability. These kinematic mounts, in conjunction with our [TECHSPEC Laser Mirrors](#), are ideal for reliable integration into laser machining, cinema or life science applications.