

86mm x 46mm x 14mm Motorized Lens Controller



Motorized Telephoto Varifocal Lenses

Stock **#22-832** **1 In Stock**

-

1

+

MRP ₹1,08,021

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,08,021 each
Need More?	Request Quote

Product Downloads

General	
Lens Accessory	Type:
Physical & Mechanical Properties	
15	Weight (g):
86mm x 46mm x 14mm	Dimensions (mm):
Hardware & Interface Connectivity	

5V (via USB or pin)		Operating Voltage (V):
Threading & Mounting		
2xM4 with plastic housing		Mounting Threads:
Regulatory Compliance		
View		Certificate of Conformance:
Bulgaria		Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000		Imported By:

Product Details

- 9-36mm Focal Length Range with Fields of View Between 10 and 39°
- NIR Corrected for Multi-Spectral and Day/Night Applications
- Manual, P-Iris and DC Auto-Iris Models Available

Mtorized Telephoto Varifocal Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing the user to zoom in on an area of interest or zoom out for full scene investigation. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination. This IR correction will keep the image sharp in daylight, at night, or when there is a mix of visible and IR illumination. Mtorized Telephoto Varifocal Lenses allow the user to optimize the field of view with 4X optical zoom capability to target an area of interest, then digitally zoom in up to 16X and are ideal for applications including Intelligent Traffic (ITS), remote sensing, security, and robotics.

Note: P-iris and DC auto-iris lenses are not compatible with standard machine vision cameras as they require a compatible auto-iris connector.