

## 6.5X Coaxial Zoom Lens, 0.7X - 4.5X Range, Inner Focus



Stock #83-894 **1 In Stock**

- 1 + MRP ₹2,71,948

**i** Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹2,71,948 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

High Magnification Zoom Lens **Type:**

In-Line Illumination **Type of Illumination:**

### Physical & Mechanical Properties

500.00 **Weight (g):**

### Optical Properties

**Horizontal Field of View, 1/2" Sensor:**

9.1 - 1.4mm

**Zoom Ratio:**

6.5:1

**Primary Magnification PMAG:**

0.7X - 4.5X

**Working Distance (mm):**

92.00

**Distortion (%):**

0.50 @ Mn FOV, 1/2" Sensor  
0.10 @ Max FOV, 1/2" Sensor

**Depth of Field (mm):**

1.8 - 0.13

**Lens Wavelength Range:**

VIS

**Numerical Aperture (NA) Range:**

0.029 - 0.069

## Sensor

**Maximum Sensor Format:**

1/2"

## Threading & Mounting

**Mount:**

C-Mount

## Regulatory Compliance

**Certificate of Conformance:**

[View](#)

**Country of Origin:**

Japan

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Robust Housing with Incremental Zoom Control
- Coaxial In-Line Illumination Option with 1/4" Fiber Port
- High Resolution Optical Design

The EO Precision Zoom Lenses are ideal for inspecting small details, especially electronic components. All lenses feature a robust, anodized aluminum housing, as well as an incremental (or detented) zoom for easy integration. With a working distance of 195mm, the 0.37X–2.23X lens is ideal for applications requiring a large object standoff or field of view. The 0.7X–4.5X lens features a working distance of 92mm and is available in coaxial or standard models. In addition, all 0.7X–4.5X lens models feature an option for an inner focus to allow them to image a large depth of field without moving the whole lens or object under inspection.