

660nm Dual Stage Free-Space Optical Isolator



660nm Dual Stage Free-Space Optical Isolator, #35-980

Stock **#35-980**

10 TO 12 DAYS

-

1

+

₹2,92,050

ADD TO CART

Qty 1+

₹2,92,050

Volume Pricing

[Request Quote](#)

Product Downloads

SPECIFICATIONS

General

Dual Stage Optical Isolator

Type:

Faraday

Style:

Physical & Mechanical Properties	
4.7	Clear Aperture CA (mm):
Optical Properties	
660	Design Wavelength DWL (nm):
80	Minimum Transmission (%):
90 (typical)	Transmission (%):
640 - 680	Wavelength Range (nm):
40 W, 4 kW/cm ² @ DWL	Damage Threshold, By Design: ☐
67	Typical Isolation at Design Wavelength (dB):
60	Minimum Isolation at Design Wavelength (dB):
40 W, 4 kW/cm ² @ DWL	Damage Threshold, CW:
Environmental & Durability Factors	
+15 to +40	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS:
View	Certificate of Conformance:

PRODUCT DETAILS

- Up to 67 dB Isolation for Ultimate Stability
- Up to 92% Transmission for Maximum Power
- 4.7mm Input Aperture

Free-Space Optical Isolators incorporate a Faraday Rotator and are specifically designed and manufactured to provide superior performance with high isolation, transmission, and power densities. Each option effectively reduces feedback in the external cavity of diode laser systems and blocks reflections from free-space fiber coupling. Free-Space Optical Isolators increase power stabilization in optical systems and also eliminate feedback-induced damage to sensitive optical components. These isolators enable state of the art protection for the most stable lasers in the world and are ideal for demanding laser applications.

