


TECHSPEC<sup>®</sup> 6mm Aperture, 150mm Length, Light Pipe Homogenizing Rod Mount



N-BK7 Light Pipe Homogenizing Rods



Stock **#64-915** 1 In Stock

-

1

+

₹12,150

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹12,150 each                  |
| Qty 6-25       | ₹9,720 each                   |
| Qty 26-49      | ₹9,090 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

Physical & Mechanical Properties

150.00Length of Compatible Light Pipe (mm):

6.00Aperture of Compatible Light Pipe (mm):


| Regulatory Compliance               |                             |
|-------------------------------------|-----------------------------|
| <a href="#">View</a>                | Certificate of Conformance: |
|                                     |                             |
| China                               | Country of Origin:          |
|                                     |                             |
| Edmund Optics India Private Limited |                             |
| Imported By:                        |                             |

## Product Details

- Homogenizes Non-Uniform Light Sources
- Hexagonal Entrance Aperture
- Uncoated and VIS-EXT Coated Options Available
- Ideal for OEM Illumination
- Additional [Light Pipe Homogenizing Rods](#) Available

TECHSPEC® N-BK7 Light Pipe Homogenizing Rods utilize total internal reflection to homogenize non-uniform light sources regardless of spectral characteristics. Their hexagonal configurations provide 35% less light loss than a comparable square configuration. Low Numerical Aperture (NA) sources require longer pipes to uniformly homogenize light, while shorter pipes will sufficiently homogenize the output from high NA sources. TECHSPEC N-BK7 Light Pipe Homogenizing Rods are made from precision N-BK7 for use in a variety of visible light applications and are available uncoated or with VIS-EXT coatings. [Fused silica versions](#) of our light pipe homogenizing rods are also available. [TECHSPEC® Light Pipe Homogenizing Rod Mounts](#), specifically designed to hold our standard and fused silica families of light pipe homogenizing rods, are available; these mounts greatly simplify the handling and integration of these components.

## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).