

[See all 11 Products in Family](#)

TECHSPEC® 6mm C Series Fixed Focal Length SWIR Lens



Stock #23-218 [CONTACT US](#)

⊖ 1 ⊕ MRP ₹37,701

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹37,701 each
Need More?	Request Quote

Product Downloads

General

C SWIR Series **Product Family:**

Fixed Focal Length Lens **Type:**

Compact Lens **Imaging Lens Type:**

Physical & Mechanical Properties

Variable	Iris Option:
48.90	Length (mm):
36.0	Maximum Diameter (mm):
36	Outer Diameter (mm):
102	Weight (g):
1.13	Maximum Rear Protrusion (mm):

Optical Properties

62.1 °	Horizontal Field of View @ Max Sensor Format:
62.1 °	Horizontal Field of View, 1/1.8" Sensor:
55.9°	Horizontal Field of View, 1/2" Sensor:
50.2°	Horizontal Field of View, 1/2.5" Sensor:
42.7 °	Horizontal Field of View, 1/3" Sensor:
32.4°	Horizontal Field of View, 1/4" Sensor:
9.00	Maximum Image Circle (mm):
0.0247	Numerical Aperture NA, Object Side:
9 (7)	Number of Elements (Groups):
900 - 1700	Wavelength Range (nm):
6.00	Focal Length FL (mm):
75 - ∞	Working Distance (mm):
Horizontal: 62.1 ° Vertical: 47.7 ° Diagonal: 75.0 °	FOV @ Max Sensor Format, H x V (mm):
f/1.4 - f/16	Aperture (f#):
900 - 1700nm BBAR	Coating:
900 - 1700nm BBAR	Coating Specification:
16.00	Entrance Pupil Position (mm):
21.35	Object Space Principal Plane (mm):
6.60	Image Space Principal Plane (mm):
-6.8	Maximum Distortion (%):
-28.78	Exit Pupil Position (mm):
SWIR	Lens Wavelength Range:

Sensor

1/1.8"	Maximum Sensor Format:
2.74	Pixel Size (µm):

Threading & Mounting

M43 x 0.75 (Male)	Filter Thread:
#85-308 (Required)	Filter Thread Adapter:
M34 x 0.5 (Female)	Front Thread:

C-Mount

Mount:

Environmental & Durability Factors

Storage Temperature (°C):

-20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

China

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Compact (C) SWIR Lens for 900-1700nm Wavelength Range
- 3.5mm to 100mm Focal Length

TECHSPEC® C Series Fixed Focal Length **SWIR** Lenses are compact, lightweight lenses designed as a low-cost alternative to the **TECHSPEC® SWIR Series Fixed Focal Length Lenses**. These lenses feature large maximum apertures, broadband AR coatings optimized for a 900 – 1700nm wavelength range, and with the working distances and resolution requirements of factory automation and inspection in mind. For optimum resolution and performance at the application's target spectral range, SWIR Machine Vision filters and **SWIR LED illumination** are recommended. TECHSPEC® C Series Fixed Focal Length SWIR Lenses are manufactured to a high tolerance, resulting in greater levels of imaging performance and low lens-to-lens variation, assuring simple installation into multiple systems. Also available with optimized performance in the **VIS** or **VIS-NIR** spectral ranges, C-Series lenses are ideal for a wide variety of machine vision, factory automation, and autonomous applications.