

[See all 10 Products in Family](#)

6mm Dia. x 12mm FL, Small Diameter Plastic Aspheric Lens



Stock **#36-628** **20+ In Stock**

- 1 + MRP ₹3,430

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹3,430 each
Qty 11-49	₹2,825 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

6.00 ±0.20 **Diameter (mm):**

Clear Aperture CA (mm):

5.00	
3.23	Edge Thickness ET (mm):
4.00 ±0.20	Center Thickness CT (mm):
	Bevel:
Protective as needed	
Optical Properties	
12.00 @550nm	Effective Focal Length EFL (mm):
0.25	Numerical Aperture NA:
9.09	Back Focal Length BFL (mm):
Acrylic V825	Substrate: <input type="checkbox"/>
±1.5	Focal Length Tolerance (%):
550	Aspheric Design Wavelength (nm):
Uncoated	Coating:
60-40	Surface Quality:
2.00	f#:
55.3	Abbe Number (v_d):
1.491	Index of Refraction (n_d):
400 - 1500	Wavelength Range (nm):
Infinite	Conjugate Distance:
550	Focal Length Specification Wavelength (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Small Diameter Eases OEM Integration
- High Numerical Apertures
- Ideal for Medical and Diagnostic Instrumentation

Small Diameter Plastic Aspheric Lenses are designed with OEM integration in mind. The small diameters, lightweight materials, and high numerical apertures make these lenses ideal for medical devices, diagnostic instrumentation, or wearable applications. Full prescription data is available to assist in design integration.

Note: For custom coating requirements, please [contact us](#).

Compatible Mounts

;