

[See all 18 Products in Family](#)

## 6" Sphere, General Purpose Integrating Sphere System



Stock #58-586 **5 In Stock**

- 1 + MRP ₹2,47,977

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹2,47,977 each
Qty 10-24	₹2,23,179 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Note:**

Included Accessories:  
SMA Adapters: [#89-652](#) (x2)  
Port Plugs: [#89-651](#) (x1)  
Port Frame Reducer: [#89-650](#) (x1)  
Port Reducer: [#89-656](#) (x1)

### Physical & Mechanical Properties

Diameter (inches):

6

2.50	<b>Diameter of 0° Port (inches):</b>
1.00	<b>Diameter of Port 2 (inches):</b>
1.00	<b>Diameter of Port 3 (inches):</b>
1.00 - 0.50	<b>Diameter of Port Frame Reducers (inches):</b>
1.00	<b>Diameter of Port Plugs (inches):</b>
2.50 - 2.00	<b>Diameter of Port Reducers (inches):</b>
1.00	<b>Diameter of SMA Adapter (inches):</b>

## Optical Properties

Spectrafect®	<b>Coating:</b>
1.7 J/cm <sup>2</sup>	<b>Damage Threshold, By Design:</b> <input type="checkbox"/>

## Threading & Mounting

1/4-20	<b>Mounting Threads:</b>
--------	--------------------------

## Environmental & Durability Factors

Up to 160°C	<b>Thermal Stability:</b>
-------------	---------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">Compliant</a>	<b>Reach 209:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Ideal for Measuring Light Sources
- Can be Upgraded to Calibrate Sensors and Test Lenses
- Designed for Simple System Integration

General Purpose Integrating Sphere Systems are designed to spatially integrate radiant flux in order to measure optical radiation. The spheres can be coupled with a sensor to create radiometers, photometers, or spectroradiometers in order to measure the total geometric flux emanating from a light source or the flux density of an illuminated area. Additionally, these sphere systems can be used to measure the output of high power lasers and laser diodes or to measure the reflectance and transmittance of materials.

A variety of accessories are available for modifying or upgrading the performance of the systems, including port plugs, port reducers, and uniform source lamps. Uniform source lamps are ideal for many irradiance applications, such as characterizing the responsivity, linearity, photo response non-uniformity, and dynamic range of focal-plan arrays. Additionally, these sources can be used for evenly illuminating test targets for evaluating the CTF of optical systems or imaging lenses, and for measuring cosine<sup>4</sup> irradiance falloff or other variations in irradiance within optical systems caused by optical aberrations.