


TECHSPEC® 7.16mm Aluminum Coated, Fused Silica Corner Cube



Stock #49-012 **20+ In Stock**

MRP ₹34,908

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹34,908 each
Qty 6-25	₹27,846 each
Qty 26-49	₹26,131 each
Need More?	Request Quote

Product Downloads

General

Retroreflector **Type:**
 Black Overpaint is 30-60 µm Thick **Note:**

Physical & Mechanical Properties

7.16 +0.00/-0.10 **Diameter (mm):**

6.10	Height (mm):
85	Clear Aperture (%):
±0.5	Height Tolerance (mm):
Optical Properties	
10	Beam Deviation (arcsec):
Aluminum with protective overcoat	Coating:
Fused Silica (Corning 7980)	Substrate: <input type="checkbox"/>
20-10	Surface Quality:
Left-Handed	Image Orientation:
Reflective Surfaces: $R_{avg} > 85\%$ FROM 400-700nm, @ 45° AOI	Coating Specification:
180	Ray Deviation (°):
400 - 700	Wavelength Range (nm):
Reflective Surfaces: 0.3 J/cm ² @ 532nm & 1064nm, 10ns	Damage Threshold, Reference: <input type="checkbox"/>
0.20	Power (fringes) @ 632.8nm:
0.20	Irregularity (fringes) @ 632.8nm:

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:
Singapore	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Incident Light is Reflected Back to the Source
- Excellent Transmission in UV
- Useful for Surveying and Alignment
- Additional [Corner Cube Retroreflectors](#) Available

TECHSPEC® UV Fused Silica Corner Cube Retroreflectors are designed to reflect any ray or beam entering the prism face, regardless of the orientation of the prism, back onto itself. A mirror will only do that at the normal angle of incidence. As a result, corner cube retroreflectors are ideal where precision alignment is difficult or time-consuming. TECHSPEC® UV Fused Silica Corner Cube Retroreflectors feature three total internal reflections and will function even at very large angles of incidence. These retroreflectors are made from UV Fused Silica which features low thermal expansion and excellent transmission throughout the UV, VIS, and NIR spectral ranges.

Technical Information

A (mm)	B (mm)	Stock No. Uncoated	Stock No. Aluminum Coated
7.16	6.1	#49-008	#49-012
12.7	10.16	#49-009	#49-013
25.4	19.05	#49-010	#49-014
50.8	38.1	#49-011	#49-015

