

## 7.30µm, 12.5mm Diameter, Infrared Longpass Filter



Infrared (IR) Longpass Filters

Stock #33-972 [CONTACT US](#)

1 
MRP ₹42,374

Price inclusive of all taxes

[ADD TO CART](#)

### Volume Pricing

Qty 1+	₹42,374 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Longpass Filter **Type:**

Transmission at cut-on wavelength is 5% of peak transmission. **Note:**

#### Physical & Mechanical Properties

12.50 +0.0/-0.1 **Diameter (mm):**

**Thickness (mm):**

1.00 ±0.2	
<10	<b>Parallelism (arcmin):</b>
90	<b>Clear Aperture (%):</b>
<b>Optical Properties</b>	
≥3.0	<b>Optical Density OD (Average):</b>
7,300.00	<b>Cut-On Wavelength (nm):</b>
Germanium (Ge)	<b>Substrate:</b> <input type="checkbox"/>
Traditional Coated	<b>Coating:</b>
80-50	<b>Surface Quality:</b>
>85 (average)	<b>Transmission (%):</b>
7670 - 14600	<b>Transmission Wavelength (nm):</b>
7.67 - 14.60	<b>Transmission Wavelength (μm):</b>
200 - 7300	<b>Blocking Wavelength Range (nm):</b>
<7	<b>Slope Factor (%):</b>
7.30 ±0.29	<b>Cut-On Wavelength (μm):</b>
3 - 5λ	<b>Surface Flatness (P-V):</b>

### Environmental & Durability Factors

-62 to +71	<b>Operating Temperature (°C):</b>
------------	------------------------------------


### Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>REACH 241:</b>
United States	<b>Country of Origin:</b>
<b>Imported By:</b> Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

## Product Details

- Coated on Silicon or Germanium Substrates
  - Ideal for Isolating Broad Spectral Regions
  - Durable, First-Surface Coatings
  - **Due to material supply chain disruptions with germanium, there may be increased lead times and price changes on our germanium products. For more information, please contact our customer service team.**
- Infrared (IR) Longpass Filters provide a sharp cut-off below a particular wavelength. Often used for order sorting, they isolate broad regions of the spectrum, simultaneously providing high transmission of desired energy, and deep rejection of unwanted energy. These filters are constructed of hard, durable first-surface dielectric coatings on optical-quality IR-transmitting substrates. Infrared (IR) Longpass Filters are able to withstand normal cleaning and handling associated with any high-quality optical component because of their make-up. These filters are particularly useful for FTIR spectroscopy and Thermal Imaging Applications. For custom sizes and coating requirements, please contact our [Sales Department](#).

## Technical Information



## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

## Compatible Mounts